



0010139


Jingweitang Industrial Zone,
Dalingshan Town, Dongguan City

Sales: Ms. Wang

Mobile number : +86 189-4861-7861

Web: [Http://www.yufengciye.com](http://www.yufengciye.com)

E-mail: yufengciye@126.com




Product Category	Core Marking			Coating Color
	Lot Number	Part Number	Inductance Grade	
Ferrite Core	2601	0010139	N/A	Green

Dimensions	Uncoated		Coated Limits			Packaging Box Qty=156 pcs
	(mm)	(in)	(mm)	(in)		
OD (A)	30.85	1.215	32.25	1.271	MAX	
ID (C)	19.25	0.758	18.25	0.719	MIN	
HT (B)	13.58	0.535	14.20	0.559	MAX	

Electrical Characeristics			Physical Characteristics						
IMPEDANCE RESULT (Testing Condition:0.65x0.5TSx120mm)			Initial Permeabili-ty	Saturation Magnetic Flux Density	Remanence	Coercivity	Density	Material	Weight (g)
@25Mhz	60Ω	26°C	900	320 (4kA/m)	140	20.0	5.1	NZO	30.0
@100Mhz	95Ω	50%							

The Limit of Breakage							Temperature Rating	
Winding Length Per Turn				Wound Coil Dimensions (mm)			Curie Temp: -30°C-110°C	
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor	OD	-	Coating Temp (Continuous up to): 180°C	
					HT	-		
				Completely Full Window	Max OD	-		
					Max HT	-		
				-	-	-		
-	-	-	-	Unwound Core			-	
-	-	-	-	40% Winding Factor		-		
							Notes:	

IMPEDANCE V.S FREQUENCY



Revision 10/8/2025

