






## SPECIFICATIONS

Current Rating: 1.5 Amps  
Insulation Resistance: 1000M $\Omega$  Min  
Contact Resistance: 20m $\Omega$  Max  
Withstanding Voltage: AC 500V  
Operation Temperature: -40°to+105°  
Contact Material: Brass  
Standard: PA6T  
Insulator Material: Polyester(UL 94V-0)  
Contact Plating: Gold Flash  
Max.Processing Temp: 240°C for 30-60seconds  
(260°C for 5 seconds)


| P/N             | PIN   | DIM.A       | DIM.B     |
|-----------------|-------|-------------|-----------|
| FH2.0-02C-01PWS | 1     | 0.00        | 2.00      |
| FH2.0-02C-02PWS | 2     | 2.00        | 4.00      |
| FH2.0-02C-03PWS | 3     | 4.00        | 6.00      |
| FH2.0-02C-04PWS | 4     | 6.00        | 8.00      |
| FH2.0-02C-05PWS | 5     | 8.00        | 10.00     |
| FH2.0-02C-06PWS | 6     | 10.00       | 12.00     |
| FH2.0-02C-07PWS | 7     | 12.00       | 14.00     |
| FH2.0-02C-08PWS | 8     | 14.00       | 16.00     |
| FH2.0-02C-09PWS | 9     | 16.00       | 18.00     |
| .....           | ..... | .....       | .....     |
| FH2.0-02C-40PWS | 40    | (PIN-1)x2.0 | (PIN)x2.0 |



## PART NUMBER DESCRIPTION:

FH2.0-02C-NPWS

(D=单排;S=双排)  
(Z=直脚;W=弯脚)  
(PIN数量;01.....40PIN)  
(排针开关)



RECOMMEND P.C.B LAYOUT  
PCB TOLERANCE:±0.05 (TOP VIEW)

|                                       |            |                                                                                                                                                |                |
|---------------------------------------|------------|------------------------------------------------------------------------------------------------------------------------------------------------|----------------|
| MANUFACTURE DWG                       |            |  东莞市讯普电子科技有限公司<br>DongGuan XunPu Electronics Co.,Ltd      |                |
| UNLESS OTHERWISE SPECIFIED TOLERANCES |            |  TITLE:2.0FH H4.3 2xnPin SMT<br>排针 W4.5 U型 PC6.5 PB4.6 6T |                |
| DECIMALS:                             | ANGLES:    | PAR                                                                                                                                            | FH2.0-02C-NPWS |
| X.±0.30                               | X°±5'      | DWN                                                                                                                                            |                |
| X.X±0.20                              | X.X°±1'    | CHKD                                                                                                                                           |                |
| X.XX±0.10                             | X.XX°±0.5' | APVD                                                                                                                                           |                |
| CUSTOMER COPY                         |            | SCALE N:A                                                                                                                                      | UNIT:MM        |
|                                       |            | SIZE:A4                                                                                                                                        | SHEET:1F1      |
|                                       |            |                                                                                                                                                | REV:A          |