



**0010263**


Jingweitang Industrial Zone,  
Dalingshan Town, Dongguan City

Sales: Ms. Wang

Mobile number : +86 189-4861-7861

Web: [Http://www.yufengciye.com](http://www.yufengciye.com)

E-mail: [yufengciye@126.com](mailto:yufengciye@126.com)



Product Category	Core Marking			Coating Color
	Lot Number	Part Number	Inductance Grade	
Ferrite Core	2601	0010263	N/A	Green

Dimensions	Uncoated		Coated Limits			Packaging Box Qty=300 pcs
	(mm)	(in)	(mm)	(in)		
OD (A)	22.51	0.887	23.64	0.931	MAX	
ID (C)	6.50	0.256	5.98	0.236	MIN	
HT (B)	13.85	0.546	15.24	0.600	MAX	

Electrical Characteristics			Physical Characteristics						
<b>IMPEDANCE RESULT</b> (Testing Condition:0.55x0.5TSx120mm)			Permeability	Saturation Magnetic Flux Density	Remanence	Coercivity	Density	Material	AL(nH/T <sup>2</sup> )
			@25Mhz	20Ω	26°C	900	320 (4kA/m)	140	20.0
@100Mhz	65Ω	50%							

WATT LOSS					Temperature Rating		
Winding Length Per Turn				Wound Coil Dimensions (mm)			Curie Temp: >180°C
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor	OD	-	Coating Temp (Continuous up to): 180°C
					HT	-	
-	-	-	-	Completely Full Window	Max OD	-	Notes:
-	-	-	-		Max HT	-	
-	-	-	-	Surface Area (mm <sup>2</sup> )			
-	-	-	-	Unwound Core	-	-	
-	-	-	-	40% Winding Factor	-	-	

**IMPEDANCE V.S FREQUENCY**

