




SPECIFICATIONS

Current Rating: 3Amps
Insulation Resistance: 1000MΩ Min
Contact Resistance: 20mΩ Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE: ±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
PH2.54-03-01PWD	1	0.00	2.54
PH2.54-03-02PWD	2	2.54	5.08
PH2.54-03-03PWD	3	5.08	7.62
PH2.54-03-04PWD	4	7.62	10.16
PH2.54-03-05PWD	5	10.16	12.70
PH2.54-03-06PWD	6	12.70	15.24
PH2.54-03-07PWD	7	15.24	17.78
PH2.54-03-08PWD	8	17.78	20.32
PH2.54-03-09PWD	9	20.32	22.86
.....			
PH2.54-03-40PWD	40	(PIN-1)X2.54	(PIN)X2.54

PART NUMBER DESCRIPTION:

PH2.54-03-NPWD

(D=单排; S=双排)
(Z=直脚; W=弯脚)
(PIN数量; 01.....40PIN)
(排针开关)

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 2.54PH H2.5 1xPin SMT PC5.0 PA6.0 PB3.2 L11.0 6T (左翻版)
			PAR PH2.54-03-NPWD
DECIMALS:	ANGLES:		DWN
X.±0.30	X°±5'		CHKD
X.X±0.20	X.X'±1"		APVD
X.XX±0.10	X.XX'±0.5'		SCALE N:A UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1 REV:A