



The Future of Analog IC Technology®

# EV2303ADN-01A

## 3A, 28V, 360kHz Synchronous Rectified Step-Down Converter EV Board

### DESCRIPTION

The EV2303ADN-01A is an evaluation board for the MP2303A, a monolithic synchronous buck regulator.

EV2303ADN evaluation board is a fully assembled and tested PCB. It generates a +3.3V output voltage at load currents up to 3A from a 4.7V to 28V input voltage range. An adjustable soft-start prevents inrush current at turn-on.

The MP2303A switches at 360kHz and achieve up to 95% efficiency with the supplied components.

### ELECTRICAL SPECIFICATIONS

Parameter	Symbol	Value	Units
Input Voltage	$V_{IN}$	4.7 – 28	V
Output Voltage	$V_{OUT}$	3.3	V
Output Current	$I_{OUT}$	3	A

### FEATURES

- 3A Output Current
- Wide 4.7V to 28V Operating Input Range
- 3.3V Output

### APPLICATIONS

- Distributed Power Systems
- Pre-Regulator for Linear Regulators
- Notebook Computers


"MPS" and "The Future of Analog IC Technology" are Registered Trademarks of Monolithic Power Systems, Inc.

### EV2303ADN-01A EVALUATION BOARD




(L x W x H) 2.0" x 1.5" x 0.5"  
(5.0cm x 3.8 x 1.2cm)

Board Number	MPS IC Number
EV2303ADN-01A	MP2303A







**PRINTED CIRCUIT BOARD LAYOUT**



**Figure 1—Top Silk Layer**



**Figure 2—Top Layer**



**Figure 3—Bottom Layer**

## QUICK START GUIDE

The output voltage of this board is preset to 3.3V. The board is laid out to accommodate most commonly used inductors and output capacitors.

1. Connect the positive and negative ends of the load to the VOUT and GND pins, respectively.
2. Connect the input voltage ( $4.7V \leq V_{IN} \leq 28V$ ) and input ground to the VIN and GND pins, respectively.
3. To turn on the MP2303A, apply an enable voltage  $V_{EN}$  to the EN pin. Drive EN higher than 1.3V to turn on the MP2303A.
4. The output voltage  $V_{OUT}$  can be programmed by varying R1. Calculate the new value using the formula:

$$R1 = R3 \times \left( \frac{V_{OUT}}{V_{FB}} - 1 \right)$$

Where  $V_{FB} = 0.8V$  and  $R3 = 10k\Omega$ .

For example, for  $V_{OUT} = 3.3V$ :

$$R1 = R3 \times \left( \frac{V_{OUT}}{V_{FB}} - 1 \right) = 10k\Omega \times \left( \frac{3.3}{0.8} - 1 \right) = 31.25k\Omega$$

for the closest standard 1% value

## RECOMMENDED COMPONENTS FOR STANDARD OUTPUT VOLTAGES

This board is programmed for most standard output voltages. The following table lists recommended components for some standard output voltages

**Table 1—Recommended Components for Standard Output Voltages**

$V_{OUT}$	R1 (1%)	R3 (1%)
0.8V	0	10k $\Omega$
1.2V	4.99k $\Omega$	10k $\Omega$
1.8V	12.4k $\Omega$	10k $\Omega$
2.5V	21.5k $\Omega$	10k $\Omega$
3.3V	31.6k $\Omega$	10k $\Omega$
5.0V	52.3k $\Omega$	10k $\Omega$

**NOTICE:** The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.