







ABIDE BY ROHS



PCB Layout (Pattern Side)



Circuit Diagram



规格：

1. 额定值：DC30V
2. 接触电阻：100mΩ Max
3. 绝缘阻抗：100MΩ Min DC250V
4. 耐电压：AC250V (50-60Hz) 1分钟
5. 全行程力：240±50gf
6. 寿命测试：100,000 Cycles
7. 全行程：2.4±0.2 mm

⑦	Terminal	—	1	Brass(0.40t)	Plating Silver	—
⑥	Hookpin	—	1	Stainless Steel	Natural	—
⑤	Contact	—	1	Copper-Silver Composite	Natural	—
④	Spring	—	1	Stainless Steel	Natural	—
③	Base	—	1	PA66	Black	—
②	Cover	—	1	PA66	White	—
①	Keystoke	—	1	PA66	Blue	—

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMAP
APPROVALS			DATE		浙江创都电子科技有限公司	
DRAWN						
CHECKED						
APPROVALS					LE:	7.0 按键开关
					PART NO.	KFC-22W77-GT-PPAK
TOLERANCES ARE			30<L	±0.30	ANGLE	UNIT: mm
			10<L≤30	±0.20		SCALE: 1:1
			5<L≤10	±0.15	±2'	PROJ: ① I
			L≤5	±0.10		DRAWING NO.
						SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			