






REV.	ECN NO.	MODIFIED MARK	APPROVED
B	—	FIRST RELEASE	



NOTES:
ELECTRICAL:
1:RATED CURRENT: 1A Max.
2:RATED VOLTAGE: 12V DC.
3:CONTACT RESISTANCE: 30 MILLIOHMS Max.
AFTER TESTING:100 MILLIOHMS Max.
4:INSULATION RESISTANCE: 100 MEGAOHMS Min.
5:DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC Min.
MECHANICAL:
1:INSERTION FORCE: 3N-30N.
2:WITHDRAWAL FORCE: 3N-30N.
3:DURRABILITY: 500 CYCLES.
ENVIRONMENTAL:
TEMPERATURE RANGE: -20°C TO 60°C.
MARK "▼" AS THE KEY CONTROL SIZE.
PIN PIN POSITION SIZE IS SUBJECT TO PCB BOARD.



SCHMATIC

PCB LAYOUT
TOP VIEW

④	TERMINAL-A	1	BRASS t=0.4	CuSn PLATED	RoHS 2.0
③	SOCKET	1	BRASS t=0.36	CuSn PLATED	
②	COVER	1	ABS	BLACK	
①	HOUSE	1	PBT	BLACK	
NO.	PART NAME	Q'TY	MATERIAL	FINISH/COLOR	REMARK
ANGLE		±5°		浙江创都电子科技有限公司	
63 < L		±0.5			
16 < L ≤ 63		±0.4			
4 < L ≤ 16		±0.3			
L ≤ 4		±0.2		TITLE: RCA PIN JACK	
TOL TABLE:		MAT'L: See table		DESIGN:	
		FINISH: See table		CHECKED:	
		Q'TY:/		APPROVED:	
		UNIT: mm		VIEW:	
		SCALE: 5:1		SHEET: 1/1	
		SIZE: A3		REV.: B	
		DWG NO.: AV-108-BK			