


NOTES:

1. CURRENT RATING: 1.5A/PIN MAX.
2. DIELECTRIC WITHSTAND VOLTAGE: 500 V AC MIN.
3. CONTACT RESISTANCE: 30 MILLIONHM MAX.
4. INSULATION RESISTANCE:1000 MΩ MIN.
5. INSERTION FORCE :35N Max.
6. UNMATING FORCE:5N Min.
7. DURABILITY:1500 CYCLES.
8. TEMPERATURE RANGE: -40 °C ~ 85 °C.
9. ALL PRODUCTS COMPLY WITH RoHS ENVIRONMENTAL REQUIREMENTS.
- 10: MARK "▼" AS THE FOCUS, FIRST ITEM INSPECTION.
- 11: MARK "⊗" TO MEASURE DIMENSIONS FOR FAI.

TABLE:

SHELL	SPCC,T=0.30mm;	NICKEL OVER ALL
CONTACT	Copper Alloy;T=0.20mm	Ni:50u"Min; Au:CONTACT AREA:1U", Solder AREA:Sn 50-120u"
PLASTIC	THERMOPLASTIC/BLACK/WHITE	-----
PART NAME	MATERIALS	FINISH



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2" X.X" ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: USB 2.0 AF 双面180° DIP 直脚无卷边	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HYCW57-USBA08-117B-X	MOLD NO.
UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO: HYC-2601080915	SHEET NO. 1 OF 1