




11: MARK "⊗" TO MEASURE DIMENSIONS FOR FAI.


A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TX1+	TX1-	VBUS	CC1	D+	D-	SBU1	VBUS			GND
	RX1+	RX1-									
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

TABLE:

		SHELL		Stainless Steel,T=0.15mm;	Ni:50u"Min
		LATCH		Stainless Steel,T=0.3mm;	Electroplated semi-nickel matte tin;50u"Min;
		INSERT MOLD	EMC SPRING	Stainless Steel;T=0.10mm	-----
			CONTACT	Copper Alloy;T=0.20mm	Ni:50u"Min; Au:CONTACT AREA:1u", Solder AREA:Sn 50-100u'
			PLASTIC	LCP(G.F30%) BLACK.	-----
P/N	PART NAME		MATERIALS		FINISH



深圳市华宇创精密电子有限公司

TOLERANCE:		DRAWN BY :	DATE :	PART NAME:	
X.X ±0.30		陈一鸣	2014-02-23	USB TYPE C 公头12P(10-2P)单排SMT铜合金款有插脚有焊	
X.XX ±0.25					
X.XXX ±0.15					
X: ±2° X.X ±0.5°		CHECKED BY:	DATE :	PART NO.	HYCW655-USBC12-133B
		马跃	2014-02-23	MOLD NO.	
UNIT: mm [inch]				APPROVED BY:	DATE :
SCALE:1:1	SIZE: A4	邱敏	2014-02-23	SHEET NO.	1 OF 1