




NOTES:

1. CURRENT RATING:
3.0A MAX.
2. DIELECTRIC WITHSTAND VOLTAGE:
100VAC.
3. TEMPERATURE RANGE:
 $-30^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
4. CONTACT RESISTANCE:
40 MILLIONHM MAX.
5. INSULATION RESISTANCE:
100 MEGOHMS MIN.
6. INSERTION FORCE :
5N~20N.
7. UNMATING FORCE:
8N~20N.
8. DURABILITY:
10,000 CYCLES.
9. ALL PRODUCTS COMPLY WITH RoHS
ENVIRONMENTAL REQUIREMENTS.
10. MARK "▼" AS THE FOCUS,
FIRST ITEM INSPECTION.
11. MARK "⊗" TO MEASURE DIMENSIONS
FOR FAI.

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-		VBUS			GND
GND			VBUS		D-	D+	CC2	VBUS			GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

TABLE:

	INSERT MOLD	SHELL	Stainless Steel,T=0.15mm;	Ni:50u"Min
		LATCH	Stainless Steel,T=0.3mm;	Electroplated semi-nickel matte tin;50u"Min;
		EMC SPRING	Stainless Steel,T=0.10mm	-----
		CONTACT	Copper Alloy,T=0.20mm	Ni:50u"Min; Au:CONTACT AREA:1u", Solder AREA:Sn 50-100u"
		PLASTIC	LCP(G.F30%) BLACK.	-----
P/N	PART NAME	MATERIALS		FINISH



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ± 0.30
X.XX ± 0.25
X.XXX ± 0.15
X.' $\pm 2'$ X.X' $\pm 0.5'$

UNIT: mm [inch]

SCALE:1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

USB TYPE C 公座14P(7+7P) 拉伸壳 夹板式有接地 L=11.5mm

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW669-USBC14-115B

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2601061644

SHEET NO.

1 OF 1