











剖面: A-A



剖面: B-B

RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm

NOTES:

1. CURRENT RATING:
3.0A MAX.
2. DIELECTRIC WITHSTAND VOLTAGE:
100VAC.
3. TEMPERATURE RANGE:
-30 °C ~ 85 °C.
4. CONTACT RESISTANCE:
40 MILLIONHM MAX.
5. INSULATION RESISTANCE:
100 MEGOHMS MIN.
6. INSERTION FORCE :
5N~20N.
7. UNMATING FORCE:
8N~20N.
8. DURABILITY:
10,000 CYCLES.
9. ALL PRODUCTS COMPLY WITH RoHS
ENVIRONMENTAL REQUIREMENTS.
- 10: MARK "▼" AS THE FOCUS,
FIRST ITEM INSPECTION.
- 11: MARK "⊗" TO MEASURE DIMENSIONS
FOR FAI.

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TX1+	TX1-		CC1	D+	D-		VBUS			GND
GND	RX1+	RX1-									GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

TABLE:

INSERT MOLD	SHELL	Stainless Steel;T=0.15mm;	Ni:50u"Min
	LATCH	Stainless Steel;T=0.3mm;	Electroplated semi-nickel matte tin;50u"Min;
	EMC SPRING	Stainless Steel;T=0.10mm	-----
	CONTACT	Copper Alloy;T=0.20mm	Ni:50u"Min; Au:CONTACT AREA:1u", Solder AREA:Sn 50-100u"
	PLASTIC	LCP(G.F30%) BLACK.	-----
P/N	PART NAME	MATERIALS	FINISH



深圳市华宇创精密电子有限公司

TOLERANCE:

X.X ±0.30
X.XX ±0.25
X.XXX ±0.15
X' ±2" X.X' ±0.5"UNIT: mm [inch]
SCALE:1:1 SIZE: A4

DRAWN BY :

陈一鸣

DATE :

2014-02-23

PART NAME:

USB TYPE C 公头9P(8+4P) 单排SMT拉伸款有插脚(插脚后移3mm)

CHECKED BY:

马跃

DATE :

2014-02-23

PART NO.

HYCW658-USBC09-144B

APPROVED BY:

邱敏

DATE :

2014-02-23

DRAW NO:

HYC-2512311634

SHEET NO.

1 OF 1