





WITH COVER




PCB LAYOUT(Tolerance:±0.05)



CIRCUIT\*1 IDENTIFIED ON THIS SURFACE (APPROX. LOCATION SHOWN FOR REF.)

REV	DESCRIPTION	DESIGN	DATE
A0			

PIN	DIM A	DIM B
2x2	3.00	9.65
2x3	6.00	12.65
2x4	9.00	15.65
2x5	12.00	18.65
2x6	15.00	21.65
2x7	18.00	24.65
2x8	21.00	27.65
2x9	24.00	30.65
2x10	27.00	33.65
2x11	30.00	36.65
2x12	33.00	39.65



**Specifications:**


- Contact resistance: ≤10mΩ
- Insulation resistance: ≥1000MΩ
- Rated voltage: 250V AC DC
- Rated current: 5.0A AC DC
- Withstand Voltage: 1000V AC/minute
- Temperature Range: -25°C ~ +85°C
- Housing: LCP UL94V-0, BLACK
- Contacts: Brass/MATTE Sn-plated
- Solder Tabs: Brass/MATTE Sn-plated

**ORDER INFORMATION:**

**A3001AWV-2\*\*-F9KB3-R-X**

PART No.:	A3001AWV-2**	SPECIAL CODE:	X=Cap
No.OF CIRCUITS:	02-24	PACKAGING:	R=REF
PLASTIC MATERIAL:	F9K=LCP	Metal code:	3=Brass
		PLATING:	B=MATTE Sn

<b>浙江创都电子科技有限公司</b>		TITLE:		3.0 Pitch Wafer 180° SMT	
		PART NO.:		MX3.0-2x*A-LT	
GENERAL TOLERANCE		USE:		PART NO.:	
X. ±0.50	X. ±5'	CUSTOMER		MX3.0-2x*A-LT	
X.X ±0.30	X.X ±2'	APPD:		DWG NO.:	
X.XX ±0.20	X.XX ±1'	CHKD:		SCALE	
⊕	∠	UNITS: mm		1 : 1	
		DR:		SHEET	
				1 / 2	



REV	DESCRIPTION	DESIGN	DATE
A0			

<b>浙江创都电子科技有限公司</b>		TITLE: 3.0 Pitch Wafer 180° SMT	
		PART NO.:	
GENERAL TOLERANCE		USE: CUSTOMER	
X. ±0.50	X. ±5°	APPD:	
X.X ±0.30	X.X ±2°	CHKD:	
X.XX ±0.20	X.XX ±1°	DR:	
		UNITS: mm	SCALE 1 : 1
			SHEET 2 / 2