


Reverse Voltage - 2000 V

Forward Current - 1 A

**FEATURES**

- For surface mounted applications
- Low profile package
- Glass Passivated Chip Junction
- Easy to pick and place
- Lead free in comply with EU RoHS 2011/65/EU directives



**MECHANICAL DATA**

- Case: SOD-123FL
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 15mg 0.00053oz

**Maximum Ratings and Electrical characteristics**


Ratings at 25 °C ambient temperature unless otherwise specified.

Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20 %.


Parameter	Symbols	EM520FL	Units
Maximum Repetitive Peak Reverse Voltage	$V_{RRM}$	2000	V
Maximum RMS voltage	$V_{RMS}$	1400	V
Maximum DC Blocking Voltage	$V_{DC}$	2000	V
Maximum Average Forward Rectified Current	$I_{F(AV)}$	1.0	A
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load	$I_{FSM}$	30	A
Maximum Instantaneous Forward Voltage at 1 A	$V_F$	1.1	V
Maximum DC Reverse Current at Rated DC Blocking Voltage	$I_R$	$T_a = 25\text{ °C}$ 2.0	$\mu\text{A}$
		$T_a = 125\text{ °C}$ 100	
Typical Thermal Resistance <sup>(1)</sup>	$R_{\theta JA}$	85	°C/W
Operating and Storage Temperature Range	$T_j, T_{stg}$	-55 ~ +150	°C

(1) P.C.B. mounted with 1.0 X 1.0" (2.54 X 2.54 cm) copper pad areas.


**Fig.1 Forward Current Derating Curve**




**Fig.2 Typical Instantaneous Reverse Characteristics**



**Fig.3 Typical Forward Characteristic**




**Fig.5 Maximum Non-Repetitive Peak Forward Surge Current**




PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SOD-123FL



The recommended mounting pad size



Marking

Type number	Marking code
EM520FL	EM520