

Features

- Operation voltage range: 2.0~6.0V
- High noise immunity
- Balanced propagation delays
- Low Power Consumption, 10- μ A Max ICC
- ESD Protection Exceeds JESD 22
 - 2000-V Human-Body Model (A114-A)
 - 200-V Machine Model (A115-A)
 - 1000-V Charged-Device Model (C101)


General Description

The TP74HC2G17 is dual buffers with Schmitt-trigger inputs. Inputs include clamp diodes. This enables the use of current limiting resistors to interface inputs to voltages in excess of VCC.

Ordering Information

ORDER NUMBER	PACKAGE DESCRIPTION	PACKAGE OPTION
74HC2G17GV	SOT23-6	Tape and Reel,3000
74HC2G17GW	SOT363	Tape and Reel,3000

Pin Configuratio




SOT23-6
SOT363

Applications

- AV Receiver
- Audio Dock:Portable
- IP Phones: Wired and Wireless
- Embedded PC
- Personal Digital Assistant(PDA)
- Power: Telecom DC/DC Module: Analog and Digital

Logic Diagram



Function Table

INPUT(nA)	OUTPUT(nY)
H	H
L	L

Note:H: HIGH voltage level;L: LOW voltage level.

Absolute Maximum Ratings

PARAMETER	SYMBOL	CONDITIONS	RATINGS	UNIT
Supply Voltage	VCC		-0.5 ~ +7.0	V
Input Voltage	VIN		-0.5 ~ +7.0	V
Output Voltage	VOUT		-0.5 ~ +7.0	V
VCC or GND Current	ICC		±50	mA
Continuous Output Current	IOUT	VOUT=0~VCC	±25	mA
Input Clamp Current	IIK	VIN<0	±20	mA
Output Clamp Current	IOK	(VOUT>VCC or VOUT<0)	±20	mA
Storage Temperature Range	TSTG		-65 ~ +150	°C
Operating Junction Temperature	TJ		-40 ~ +125	°C
Junction to Ambient	θ_{JA}	SOT-23-6	230	°C/W
		SOT363	280	°C/W

Note:

Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

Recommended Operating Conditions (TA =25°C, unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Supply Voltage	VCC	Operating	2.0	5.0	6.0	V
Input Voltage	VIN		0	5.0	VCC	V
Output Voltage	VOUT		0	5.0	VCC	V


Electrical Characteristics (TA =25°C, unless otherwise specified)

PARAMETER	SYMBOL	TEST Conditions	MIN	TYP	MAX	UNIT
positive-going threshold voltage	VT+	VCC=3.0V	--	2.0	1.5	V
		VCC=4.5V	--	3.0	3.15	V
		VCC=6.0V	--	3.6	4.2	V
negative-going threshold voltage	VT-	VCC=3.0V	0.3	1.5	--	V
		VCC=4.5V	1.35	2.3	--	V
		VCC=6.0V	1.65	2.9	--	V
hysteresis voltage	VH	VCC=3.0V	0.3	--	1.2	V
		VCC=4.5V	0.4	--	1.4	V
		VCC=6.0V	0.5	--	1.7	V
High-Level Output Voltage	VOH	VCC=2.0V, IOH=-20μA	1.9	2.0	--	V
		VCC=4.5V, IOH=-20μA	4.4	4.5	--	V
		VCC=6.0V, IOH=-20μA	5.9	6.0	--	V
		VCC=4.5V, IOH=-4.0mA	4.18	4.32	--	V
		VCC=6.0V, IOH=-5.2mA	5.68	5.81	--	V
Low-Level Output Voltage	VOL	VCC=2.0V, IOL= 20μA	--	0	0.1	V
		VCC=4.5V, IOL= 20μA	--	0	0.1	V
		VCC=6.0V, IOL= 20μA	--	0	0.1	V
		VCC=4.5V, IOH= 4.0mA	--	0.15	0.26	V
		VCC=6.0V, IOH= 5.2mA	--	0.16	0.26	V
Input Leakage Current	Ii	VIN=6.0V or GND	--	--	±0.1	uA
Quiescent Supply current	Iq	VIN=VCC or GND, IOU=0A	--	--	1.0	uA
input capacitance	CI		--	2.0	--	pF

Dynamic characteristics (TA =25°C , unless otherwise specified)

PARAMETER	SYMBOL	TEST Conditions	MIN	TYP	MAX	UNIT	
propagation delay	tpd	CL=50pF	VCC=2.0	--	22	78	nS
			VCC=4.5	--	21	29	nS
			VCC=6.0	--	6.0	26	nS
transition time	tt	CL=50pF	VCC=2.0	--	18	76	nS
			VCC=4.5	--	6.0	15	nS
			VCC=6.0	--	5.0	13	nS
power dissipation Cap	CPD	VI = GND to VCC	--	10	--	pF	

TEST CIRCUIT AND WAVEFORMS




Definitions test circuit:

R_L = Load resistance.

C_L = Load capacitance including jig and probe capacitance.

R_T = Termination resistance should be equal to output impedance Z_o of the pulse generator.

Testcircuitformeasuringswitchingtimes




Notes:

1. VOL and VOH are typical output drop that occur with the output load.
2. tPLH and tPHL are the same as tPD .

Package information

SOT363 (Unit: mm)



Mounting Pad Layout (unit: mm)

