





NOTE:1

1. ELECTRICAL CHARACTERISTICS:
 - 1.1 CURRENT RATING: 0.5A MAX.
 - 1.2 IMPEDANCE:500HM NOMINAL.
2. MECHANICAL CHARACTERISTICS:
 - 2.1 OPERATING TEMP. $-40^{\circ}\sim 90^{\circ}$
 - 2.2 VEWR UP TO 3GHz:1.3MAX.
3GHz TO 6GHz:1.4MAX.
 - 2.3 DURABILITY:30CYCLES



NOTE:2


- 1.HOUSING MATERIAL: LCP, NATURE, UL94V-0.
- 2.TERMINAL MATERIAL: COPPER ALLOY (C2680),
- 3.SHELL MATERIAL: COPPER ALLOY (C5191),

RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05

3	GROUND CONTACT	1	COPPER ALLOY	Au PLATING OVER NI OVER ALL	
2	INNER CONTACT	1	COPPER ALLOY	Au PLATING OVER NI OVER ALL	
1	HOUSING	1	LCP UL94V-0		
ITEM	DESCRIPTION	Q'TY	MATERIAL	FINISH	REMARK

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd			
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:RF BOARD END CONNECTOR,FIRST GENERATION		
			PAR		IPEX-002
			DWN	Lucas	
			CHKD	Ethan	
DECIMALS:			ANGLES:		
.X:±0.25	.X':±5°				
.XX:±0.25	.XX':±3°				
.XXX':±1°					
CUSTOMER COPY			SIZE:A4	SHEET:1F1	REV:A

PULL OUT DIRECTION (拉出方向)



NOTES(备注):

- MATERIAL(材料):
 - EMBOSSED CARRIER(载带): PET
 - COVER TAPE(盖带): PET
 - REEL(卷盘): PS
 - SHIPPING CARTON(包装箱): CORRUGATED FIBER(多层瓦楞纸)
- DIMENSION(尺寸):
 - REEL(卷盘): W=12.5
 - SHIPPING CARTON(包装箱): L=350, W=350, H=190
- QUANTITY(数量):
 - PRIMARY PACKING(基本包装): 5000PCS/REEL
 - CRITERION PACKING(标准包装): 10REELS/CARTON(10卷/箱50000PCS)
- WEIGHT(重量):
 - NET WEIGHT(净重): 0.50KG/REEL.
 - GROSS WEIGHT(总重): 0.50KG/REEL, 5.5KG/CARTON.
- PEELING RESISTANCE(盖带剥离力): 10gf~130gf.

320mm MIN
(EMPTY空带)


PULL OUT DIRECTION (拉出方向)

80mm MIN
(COVER TAPE上盖带)




COMPONENTS组成成分

320mm MIN(EMPTY)

PULL OUT DIRECTION (拉出方向)



MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			
DECIMALS:	ANGLES:	SCALE 1:1	UNIT:MM
X.X $\pm$ 0.15	.° $\pm$ 2.0°	SIZE:A4	SHEET:1F1
X.XX $\pm$ 0.05	X.° $\pm$ 2.0°	CUSTOMER COPY	REV:A
X.XXX $\pm$ 0.05	X.X° $\pm$ 1.0°		



品名 NAME: _____

料号 PART No.: _____

客户料号 CLIENT P/N: _____


客户订单 CLIENT PO#: _____

数量 Q'TY: _____ 重量 WEIGHT: _____

批次 LOT No.: _____

日期 DATE: _____

ID LABEL



MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd		
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: MICRO RF I BAORD SMT 4 PADS TYPE	
			PAR	IPEX—002
DECIMALS:	ANGLES:		DWN	
X.X±0.15	.°±2.0°		CHKD	
X.XX±0.05	X.°±2.0°		APVD	
X.XXX±0.05	X.X°±1.0°	CUSTOMER COPY	SCALE:1:1	UNIT:MM
			SIZE:A4	SHEET:1F1
				REV:A