


Specification of MEMS Microphone

RoHS Compliance & Halogen Free

LinkMems P/N: LMA2718T381-OAC03



Designed by	Checked by	Approved by
Kevin	Thomas	Hary

Customer Approval

Approved by:_____



Contents

1. Introduction	3
2. Electrical Characteristics	3
3. Frequency Response Curve	4
3.1. Frequency Response Curve	4
3.2. Phase Response Curve	4
4. Test Setup	4
5. Measurement Circuit	5
6. Mechanical Characteristics	5
6.1. Weight	5
6.2. Appearance Drawing	5
7. Application	6
7.1. Pickup Tool Pick Location & PCB Solder Pad Layout	6
7.2. Recommended Reflow Process Condition	6
7.3. Storage Condition	6
8. Packaging	7
8.1. Tape & Reel Specification	7
8.2. Packaging Information	8
9. Reliability Test	9

MEMS Microphone

1. Introduction

The LMA2718T MEMS Microphones are integrated with specialized Pre-amplification ASIC to provide high sensitivity, high SNR output from a capacitive audio sensor. It's packaged for surface mounting and high temperature reflow assembly.


2. Electrical Characteristics

Test Condition: $V_{DD}=2.0V$, $23\pm 2^{\circ}C$, $55\pm 10\%R.H.$, unless otherwise specified.


Specification	Symbol	Test Conditions		Min.	Typ.	Max.	Unit
Directivity				Omni-directional			
Sensitivity Range	S	94dB SPL @1kHz		-39	-38	-37	dB
Output Impedance	Z_{out}	94dB SPL @1kHz				300	Ω
Current Consumption	I				120		μA
S/N Ratio	SNR	94dB SPL @1kHz A-Weighted			62		dB(A)
Operating Voltage	V_{DD}			1.6	2.0	3.6	V
Total Harmonic Distortion	THD	94dB SPL @1kHz			0.1	0.5	%
Sensitivity Drop	ΔS	94dB SPL @1kHz $V_{DD}=3.6V\sim 1.6V$				0.5	dB
Acoustic Overload Point	AOP	10% THD @1kHz			127		dB SPL
Power Supply Rejection	PSR	100mVpp Square wave@217Hz, A-weighted			-100		dB
Phase Response	PR	94dB SPL, measured in free field and normalized at the average value of the Golden Mics	20Hz	-5		5	deg
			3kHz	-5		5	

3. Response Curve


3.1 Frequency Response Curve




3.2 Phase Response Curve



4. Test Setup (Sensitivity Test in Anechoic Room)




5. Measurement Circuit



6. Mechanical Characteristics


6.1 Weight: Less than 0.03g

6.2 Appearance Drawing(unit: mm)




7. Application

7.1 Pickup Tool Pick Location& PCB Solder Pad Layout



7.2 Recommended Reflow Process Condition

Recommend reflow profile, solder reflow $\leq 260^{\circ}\text{C}$ (for 30s Max of peak temperature).



Important Notes

In order to minimize device damage:

1. Do not wash or clean the boards after the reflow process.
2. Do not apply the airflow which pressure over 0.3MPa blow into the port hole within a distance of less than 5 cm.
3. Do not exposed to ultrasonic processing or cleaning.
4. Do not pull a vacuum over port hole of the microphone.

7.3 Storage Condition


7.3.1 Storage temperature range:-40 $\sim$ +100 $^{\circ}\text{C}$,and humidity is less than 75%.

7.3.2 Operating temperature range:-40 $\sim$ +85 $^{\circ}\text{C}$.


7.3.3 MSL (moisture sensitivity Level) is Class 1.

8. Packaging

8.1 Tape & Reel Specification



8.2 Packaging Information



9. Reliability Test

The samples should be placed in the room with $23\pm 2^{\circ}\text{C}$, $55\pm 10\%\text{R.H.}$ for 2 hours at least before final measurement, unless otherwise specified.

Item	Detail	Standard
Simulated Reflow (Without Solder)	Samples for qualification testing require 3 times $260\pm 5^{\circ}\text{C}$ reflow solder profiles. 2 hours of setting time is required between each reflow profile test.	$\pm 3\text{ dB}$
Static Humidity	Precondition at $+25^{\circ}\text{C}$ for 1 hour. Then expose to $+85^{\circ}\text{C}$ with 85% relative humidity for 240 hours.	$\pm 3\text{ dB}$
Temperature Shock	Each cycle shall consist of 30 minutes at -40°C , 30 minutes at $+125^{\circ}\text{C}$ with 5 minutes transition time. Test duration is for 30 cycles, starting from cold to hot temperature.	$\pm 3\text{ dB}$
ESD Sensitivity	According to MIL-STD-883G, Method 3015.7 for Human Body Model. Discharge Position: I/O pins Charge Voltage: $\pm 3000\text{V}$ Discharge Network: 100pF & 1500Ω	$\pm 3\text{ dB}$
Random Vibrations	Vibrate randomly along three perpendicular directions for 30 minutes in each direction, 4 cycles from 20Hz ~ 2000Hz with a peak acceleration 20g .	$\pm 3\text{ dB}$
Mechanical Shock	Subject samples to half sine shock pulses ($3000\text{g}\pm 15\%$ for 0.3ms) in each direction, totally 18 shocks.	$\pm 3\text{ dB}$
High temperature Storage	Microphone unit must maintain sensitivity after storage at $+105^{\circ}\text{C}$ for 240 hours.	$\pm 3\text{ dB}$
Low temperature Storage	Microphone unit must maintain sensitivity after storage at -40°C for 240 hours.	$\pm 3\text{ dB}$
Drop Test	The test was repeated in six directions for 3 times, Dropped from 1.5m height on to a steel surface, total 18 times and inspected for mechanical damage.	$\pm 3\text{ dB}$

Specification Revisions

Revision	Description	Approved	Date
1.2	New Version Released	Hary	17/05/2024
1.3	Update Electrical Characteristics	Hary	15/12/2025