



REV.	ECN NO.	REVISED	DATE





NOTE:

1.MATERIAL:

- a.HOUSING:PBT UL 94V-0
- b.CONTACT:PHOSPHOR BRONZE
(SURFACE PLATING:Sn=100u"-120u")
SEE ORDERING INFORMATION

2.ELECTRIC:

- a.CONTACT RESISTANCE: 30 MILLIOHMS MAX
- b.INSULATION RESISTANCE: 1000 MEGA OHMS MIN
- c.DIELECTNIC VOLTAGE: 500V AC ONE SEC LEVEL
- d.OPERATING TEMPERATURE: -35°C~ +85°C



PCB Layout Diagram
Top View

3	TERMINAL(-)	1	PHOSPHOR BRONZE, T=0.20mm	Sn Plating
2	TERMINAL(+)	1	PHOSPHOR BRONZE, T=0.40mm	Sn Plating
1	HOUSING	1	PBT	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		深圳市连欣科技有限公司			
DECIMALS: X :±0.30 X X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND	YangFeng	DATE	2021.10.28
WEIGHT: 1.56g		CHKD	ZhouRuicai	DATE	2021.10.28
SHEET 1 OF 1		APVD	XueShunyong	DATE	2021.10.28
SCALE: 2:1		SIZE: A4	VIEW:	TITLE: BS-CR2032-9电池座DIP	
UNIT: mm		REV.: A/1	OBJECT: MY	PART NO.: XDBS-CR2032-9	
DRAW NO: MY-CP-0026					