





SPECIFICATION
 1.Rating : DC12V 50mA.
 2.Contact resistance: ≤100mΩ.
 3.Insulation resistance: ≥100MΩ (DC250V).
 4.Withstanding voltage: 250VAC .
 5.Operating Force: 160±50gf./250±80gf
 6.Travel:0.25±0.1mm.
 7.Life test: 10,000 cycles.
 8.Operation temperature range:-25℃~85℃.

Circuit



发红光 L2⊕ → ⊖ L1
 发蓝光 L1⊕ → ⊖ L2
 双色灯



P.C.B Layout

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		REVISIONS		BY APPD	
7	COVER	PC	1		<1.5: ±0.1mm	ANGULAR	AO	2025.07.01	首次发行	LP
6	COVER	PET	1		>1.5~5.0: ±0.25mm	±1°	NO	DATE		
5	TERMINAL	BRASS	4	Ag-PLATED	>5.0: ±0.3mm					
4	CONTACT	PHOSPHOR BRONZE	1		TITLE: TACT SWITCH		UNIT : MM	ROHS COMPLIANT	DWN	
3	LED	GaAsP/GaP	1		MODEL: TC-1193RB-RL-C-01		SCALE: 1:1		CHK'D	
2	BUTTON	PA66	1						APPD	
1	HOUSING	PA66	1							
					DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 HOOYA 东莞市弘皓电子有限公司			PRO.AGL:		REV :AO