



1-2379006-1 AS SHOWN




CODING CONFIGURATION AS SHOWN


CODING A




CODING B



CODING C





CODING D



NOTES:

1. THE PRODUCT IS SUPPLIED WITH LEVER IN CLOSED POSITION
2. INTERFACE DRAWING: 114-32367
3. MATING PARTS:
20P SOCKET HOUSING: 2379013-1 COD 1 ; 2379013-2 COD 2
SECONDARY LOCK: 2379014-1
4. SUITABLE TERMINALS SEE TABLE

TERMINAL	WIRE RANGE MM ²	PART NO.	REMARK
MQS0.64	0.8~0.22	1355717	SEE DRAWING 929454
	0.13/0.17	2141824	
	0.25~0.35	928999	
	0.5~0.75	963715	
MCP2.8	0.25~0.5	2141857	SEE DRAWING 1355036
	0.5~1.0	968849	
	1.5~2.5	968851	








1	1	1	1	1	1	1	1	LEVER HOUSING	PBT-GF	BLACK	2
1				1				HOUSING, CODING D	PBT-GF	BROWN	1
	1				1			HOUSING, CODING C	PBT-GF	NATURE	1
		1				1		HOUSING, CODING B	PBT-GF	GRAY	1
1-2379006-4	1-2379006-3	1-2379006-2	1-2379006-1	2379006-4	2379006-3	2379006-2	2379006-1	HOUSING, CODING A	PBT-GF	BLACK	1
LEVER AT MQS SIDE								DESCRIPTION	MATERIAL	COLOR	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.				OWN	J.LEE	22SEP2020	 TE Connectivity			
DIMENSIONS:				CHK	J.ZONG	22SEP2020				
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD	J.YIN	22SEP2020				
mm		0 P L C 1 P L C 2 P L C 3 P L C 4 P L C ANGLES FINISH		+ ± ± ± ± ± ±		NAME		BCM 52P HYBRID PLUG, ASSEMBLY 40POSN 0.64MM, 12POSN 2.8MM		
						PRODUCT SPEC				
MATERIAL		SEE TABLE				APPLICATION SPEC				
						WEIGHT		-		
						SIZE		CAGE CODE		
						A		00779		
						C=		2379006		
						DRAWING NO		RESTRICTED TO		
								-		
						CUSTOMER DRAWING				
						SCALE		2:1		
						SHEET		1 OF 3		
						REV		A3		

4-2379006-1 AS SHOWN

THE OTHER DIMENSIONS NOT DEFINED ON THIS SHEET REFER TO SHEET 1/3



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

- NOTES:
- THE PRODUCT IS SUPPLIED WITH LEVER IN CLOSED POSITION
 - INTERFACE DRAWING: 114-32367
 - MATING PARTS:
20P SOCKET HOUSING: 2379013-1 COD 1 ; 2379013-2 COD 2
SECONDARY LOCK: 2379014-1
 - SUITABLE TERMINALS SEE TABLE




TERMINAL	WIRE RANGE MM ²	PART NO.	REMARK
MQS0.64	0.8~0.22	1355717	SEE DRAWING 929454
	0.13/0.17	2141824	
	0.25~0.35	928999	
	0.5~0.75	963715	
MCP2.8	0.25~0.5	2141857	SEE DRAWING 1355036
	0.5~1.0	968849	
	1.5~2.5	968851	

1	1	LEVER HOUSNG	PBT-GF	GRAY	2
1	1	HOUSING, CODING A	PBT-GF	BLACK	1
5-2379006-1	4-2379006-1	DESCRIPTION	MATERIAL	COLOR	ITEM
LEVER AT MQS SIDE	LEVER AT MCP SIDE				



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.LEE CHK J.ZONG APVD H.YIN	22SEP2020 22SEP2020 22SEP2020	TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
MM		0 PLC ±- 1 PLC ±0.3 2 PLC ±0.2 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH ±-		PRODUCT SPEC	
				APPLICATION SPEC	
MATERIAL		WEIGHT		SIZE CAGE CODE DRAWING NO	
- SEE TABLE		-		A 00779 C=2379006	
		CUSTOMER DRAWING		RESTRICTED TO	
		SCALE 2:1		SHEET 2 OF 3	
				REV A3	

2-2379006-1 AS SHOWN

THE OTHER DIMENSIONS NOT DEFINED ON THIS SHEET REFER TO SHEET 1/3



DETAIL A
SCALE 10:1




NOTES:


1. THE PRODUCT IS SUPPLIED WITH LEVER IN CLOSED POSITION
2. INTERFACE DRAWING: 114-32367
3. MATING PARTS:
20P SOCKET HOUSING: 2379013-1 COD 1 ; 2379013-2 COD 2
SECONDARY LOCK: 2379014-1
4. SUITABLE TERMINALS SEE TABLE

△ 4.0MM2 TERMINAL PART NO.: 968853 WIRE RANGE: 2.7~3.7MM
INSOLUTION CRIMPED AREA OD=4.5MM MAX.

TERMINAL	WIRE RANGE MM ²	PART NO.	REMARK
MQS0.64	0.8~0.22	1355717	SEE DRAW ING 929454
	0.13/0.17	2141824	
	0.25~0.35	928999	
	0.5~0.75	963715	
MCP2.8	0.25~0.5	2141857	SEE DRAW ING 1355036
	0.5~1.0	968849	
	1.5~2.5	968851	
	4.0△	968853	



4.0MM2 TERMINAL PART NO.: 968853 WIRE RANGE: 2.7~3.7MM
INSOLUTION CRIMPED AREA OD=4.5MM MAX.

A3	1	1	1	1	LEVER HOUSING	PBT-GF	BLACK	2	
	1				HOUSING, CODING D	PBT-GF	BROWN	1	
		1			HOUSING, CODING C	PBT-GF	NATURE	1	
			1		HOUSING, CODING B	PBT-GF	GRAY	1	
				1	HOUSING, CODING A	PBT-GF	BLACK	1	
2-2379006-4	2-2379006-3	2-2379006-2	2-2379006-1		DESCRIPTION	MATERIAL	COLOR	ITEM	
LEVER AT MCP SIDE									
THIS DRAWING IS A CONTROLLED DOCUMENT.					TE Connectivity				
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.3 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±0.5 FINISH ±0.5		DWN FILE 22SEP2020	NAME BCM 52P HYBRID PLUG, ASSEMBLY 40POSN 0.64MM, 12POSN 2.8MM -	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				CHK J.ZONG 22SEP2020					
		APVD I.YIN 22SEP2020		PRODUCT SPEC -					
		APPLICATION SPEC -							
MATERIAL -	-		WEIGHT -	A1	00779	2379006	-		
SEE TABLE					CUSTOMER DRAWING		SCALE 2:1	SHEET 3 OF 3	REV A3