

1

2

3

4

5








A

B

C

D

E



GT-A1008H M -2 XX X 01

**G-Switch**  
**Series No**  
**Connector**  
 H-Housing  
**M-Male**

**Housing Colour**  
 W-White

**Pin Q' PY**  
 16-50

**Row NO**  
 2-Dual Rows

**G-Switch Specification:**

- 1.Current rated: 1.0A AC/DC
- 2.Voltage rating: 100V AC/DC
- 3.Withstanding voltage: 250V AC
- 4.Contact resistance: 20mΩ max.
- 5.Insulation resistance: 100MΩ min
- 6.Durability cycle: 30Cycles
- 7.Removal force: 0.3kgf/Pin min
- 8.Operating temperature range: -40°C ~ +105°C

**Ordering Information:**

Circuit	Dimensions(mm)			Circuit	Dimensions(mm)		
	A	B	C		A	B	C
16	7.00	9.70	8.30	28	13.00	15.70	14.30
20	9.00	11.70	10.30	30	14.00	16.70	15.30
22	10.00	12.70	11.30	36	17.00	19.70	18.30
24	11.00	13.70	12.30	40	19.00	21.70	20.30
26	12.00	14.70	13.30	50	24.00	26.70	25.30

1	HOUSING	PA66,94V-0	WHITE
NO.	PART NAME	MATERIAL	REMARK



SCALE: 1:1 UNIT: mm  
 SIZE: A4

Unless otherwise General Tolerance:  
 X ±0.40  
 X.x ±0.30  
 X.xx ±0.20  
 X\* ±5°  
 X.x° ±3°

Title: Housing 1.00mm Pitch Dual Rows Male

Molde Code: GT-A1008HM-2XXX01

DRAWN	CHECKED	APPROVED	DATE
Hu	Hu	Chen	2021.10.20



REV: A0 SHEET: 1/1

1

2

3

4

5