

A

B

C

D

E

F

G

A

B





C

D

E

F

G



材料及电镀

- ①. 螺丝: M2.0, 钢, 镀锌, 一字槽
- ②. 塑件主体: PA66
- ③. 夹子: 磷青铜, 镀镍
- ④. 方盒: 黄铜, 镀镍
- ⑤. 塑件盖板: PA66

电气性能

- 额定电压: 300V 250V
- 额定电流: 8A 7A
- 接触电阻: 20mΩ (Max)
- 绝缘电阻: 500MΩ\DC500V
- 耐电压: AC1500V\1Min
- 使用线径: 28-16AWG 0.5-1.5mm<sup>2</sup>

机械性能

- 温度范围: -40℃ ~ +105℃
- 瞬时温度: +250℃ 5秒
- 扭力: 0.2N.m(2.04kgf.cm)
- 剥线长度: 6-7mm

2	方盒	铜	镀镍	
1	基座	PA66	绿色	
序号	品名	材质	电镀/颜色	备注

 深圳市虹成电子有限公司 GENERAL TOLERANCES (UNLESS SPECIFIED)	品名 TITLE	接线端子		
	料号 PART NO	HC-JXDZK-3.5-14P		
比列 SCALE	1:1	制图 DRAW	AhYe	
单位 UNIT	MM	审核 CHECKED	夏操云	
张数 PART NO	1 OF 1	批准 APPROVE	赵亮亮	
版本 REV	A			

公差参数			
Poles	Dim	Dim P	Dim L
2-6P		±0.10	±0.20
7-12P		±0.20	±0.30
13-18P		±0.25	±0.40
19-24P		±0.30	±0.50