




NOTES:

备注


- 1.Brass or purple copper,Bright tin-plating  
黄铜或紫铜, 镀亮锡
- 2.Wire screw hole M5  
压线螺孔M5
- 3.Current Rating: 黄铜100A/紫铜150A  
额定电流:黄铜100A/紫铜150A
4. There shall be no defects such as pin deformation and burrs.  
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances  
未标注的尺寸参考公差



**Ordering Information**

HC - \* \*\* \* \* - \*\* \* - \* \*\* \* \* - 07

Type	Thickness	Screw Threads	Welding Feet	Series	D=01P	Product No.	Material
M-111 Tooth (铆牙)	10~1.0mm	3~M6 (铆牙)	(焊脚)	1620~1620mm	D=01P	产品序号	铜(Copper)
W-111 Nut (铆螺母)	12~1.0mm	4~M6 (铆牙)	2~5个	.....	D=01E		紫铜(Copper)
W-111 Gasket (铆垫片)	15~1.5mm	6~M6 (铆牙)	4~4个		D=01ag		紫铜(Copper)
	20~2.0mm	6~M6 (铆牙)	6~6个				
	25~2.5mm		8~8个				
	30~3.0mm		.....				



			GENERAL TOLERANCE	制图	07	<b>深圳市华灿天禄电子有限公司</b> ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核					
			5 or more ±0.35	批准		产品名称	PCB 焊接端子 厚度1.5 插板 铆垫片	版本	A
			2~5 ±0.25	比例		产品料号	M5 6焊脚 14.5x14.5x12.5mm	REV.	
			0~2 ±0.15	投影		材料	HC-RG1556-1414-D729RC-07	单位	mm
序号	变更内容	日期	Angle ±3.0°	投影		材料		页次	1/1
No.	MODIFY CONTENT	MODIFY DATE		Projection		MATERIAL		SHEET	