







电气特性/Electrical Specification	
额定参数/Rated	250V 10A
接触电阻/Contact Resistance	20mΩ MAX
绝缘电阻/Insulation Resistance	5000mΩ/1000V
抗电强度/Dielectric Strength	2000V/1 min
机械特性/Mechanical Specification	
使用温度/Temp range	-40° C ~ +105° C
扭矩/Torque	0.4Nm
线径/Wire range	AWG12~28
剥线长度/Strip length	7.0~8.0mm
瞬间温度/MAX Soldering	+250° C/5s
部件材质/Part&Material	
塑件/Housing	PA66 UL94 V-0
螺丝/Screws	钢 镀锌/Steel Zn plating
方块/Cage	黄铜 镀镍/Brass Ni plating
端子/Terminal	磷青铜 镀银/Phosphor Bronze Ni plating

间距公差/Spacing tolerance(mm)								 连兴旺电子(深圳)有限公司 LXWCONN ELECTRONICS (SHENZHEN) CO., LTD										PART NAME:			
X.	X.X	X.X.X		0.1/10														PART NO:LXW5.08GK-NP			
±0.5	±0.30	±0.1		±2°		DRAWING NO:															
未注公差/General tolerances(mm)																					
0---30	31---50	51---80	81---120		>121	STATUS	APPD	CHKD	DRFT	DATE	CUSTOM	PROJECT	UNITS	TYPE: CUSTOMER DRAWINGS							
±0.30	±0.50	±0.70	±1.05		±1.20		ZH							MM		REV	SIZE	SHEET			
																A	A4	1/1			