



QNHCHIP

QN4606C

# Product Specification

QN4606C

---

30V Complementary MOSFET




## FEATURES

- N-Channel: 30V, 9A  
 $R_{DS(ON)} < 27m\Omega @ V_{GS} = 10V$   
 $R_{DS(ON)} < 37m\Omega @ V_{GS} = 4.5V$
- P-Channel: -30V, -7A  
 $R_{DS(ON)} < 46m\Omega @ V_{GS} = -10V$   
 $R_{DS(ON)} < 72m\Omega @ V_{GS} = -4.5V$
- Excellent Gate Charge x  $R_{DS(ON)}$  Product(FOM)
- Very Low On-resistance  $R_{DS(ON)}$
- Fast Switching Speed

## Applications

- Battery Protection
- Load Switch
- Power Management

## Pin Description





## Absolute Maximum Ratings

(@  $T_A = 25^\circ\text{C}$  unless otherwise specified)

Symbol	Parameter	Max. N-Channel	Max. P-Channel	Units
$V_{DSS}$	Drain-Source Voltage	30	-30	V
$V_{GSS}$	Gate-Source Voltage	$\pm 20$	$\pm 20$	V
$I_D$	Continuous Drain Current	$T_A=25^\circ\text{C}$	-7	A
		$T_A=100^\circ\text{C}$	-4.6	A
$I_{DM}$	Pulsed Drain Current <sup>(1)</sup>	36	-28	A
$E_{AS}$	Single Pulsed Avalanche Energy <sup>(2)</sup>	12	30	mJ
$P_D$	Power Dissipation	$T_A=25^\circ\text{C}$	2.5	W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	46.3	50	$^\circ\text{C}/\text{W}$
$T_J, T_{STG}$	Operating and Storage Temperature Range	-55 to +150		$^\circ\text{C}$



## N-Channel Electrical Characteristics

( $T_J = 25^\circ\text{C}$  unless otherwise specified)

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Units
<b>Off Characteristic</b>						
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	30	-	-	V
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS}=30V, V_{GS}=0V$	-	-	1	$\mu A$
$I_{GSS}$	Gate to Body Leakage Current	$V_{DS}=0V, V_{GS}=\pm 20V$	-	-	$\pm 100$	nA
<b>On Characteristics</b>						
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu A$	1.0	1.4	2.0	V
$R_{DS(on)}$	Static Drain-Source on-Resistance <sup>(2)</sup>	$V_{GS}=10V, I_D=5A$	-	17	27	m $\Omega$
		$V_{GS}=4.5V, I_D=3A$	-	25	37	m $\Omega$
<b>Dynamic Characteristics</b>						
$C_{iss}$	Input Capacitance	$V_{DS}=15V, V_{GS}=0V, f=1.0MHz$	-	335	-	pF
$C_{oss}$	Output Capacitance		-	54	-	pF
$C_{rss}$	Reverse Transfer Capacitance		-	44	-	pF
$Q_g$	Total Gate Charge	$V_{DS}=15V, I_D=5A, V_{GS}=10V$	-	5.2	-	nC
$Q_{gs}$	Gate-Source Charge		-	0.9	-	nC
$Q_{gd}$	Gate-Drain("Miller") Charge		-	1.3	-	nC
<b>Switching Characteristics</b>						
$t_{d(on)}$	Turn-on Delay Time	$V_{DS}=15V, I_D=3A, V_{GS}=10V, R_{REN}=3\Omega$	-	4.5	-	ns
$t_r$	Turn-on Rise Time		-	2.5	-	ns
$t_{d(off)}$	Turn-off Delay Time		-	14.5	-	ns
$t_f$	Turn-off Fall Time		-	3.5	-	ns
<b>Drain-Source Diode Characteristics and Maximum Ratings</b>						
$I_S$	Maximum Continuous Drain to Source Diode Forward Current		-	-	9	A
$I_{SM}$	Maximum Pulsed Drain to Source Diode Forward Current		-	-	36	A
$V_{SD}$	Drain to Source Diode Forward Voltage	$V_{GS}=0V, I_S=9A$	-	0.8	1.2	V

Notes:

- Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
- $E_{AS}$  condition :  $T_J=25^\circ\text{C}, V_{DD}=15V, V_G=10V, L=0.5mH, R_g=25\Omega, I_{AS}=7A$
- Pulse Test: Pulse Width  $\leq 300\mu s$ , Duty Cycle  $\leq 0.5\%$



## P-Channel Electrical Characteristics

( $T_J = 25^\circ\text{C}$  unless otherwise specified)

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Units
<b>Off Characteristic</b>						
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D = -250\mu A$	-30	-	-	V
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS} = -30V, V_{GS}=0V,$	-	-	-1	$\mu A$
$I_{GSS}$	Gate to Body Leakage Current	$V_{DS}=0V, V_{GS}= \pm 20V$	-	-	$\pm 100$	nA
<b>On Characteristics</b>						
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D = -250\mu A$	-1.0	-1.5	-2.0	V
$R_{DS(on)}$	Static Drain-Source on-Resistance <sup>(3)</sup>	$V_{GS} = -10V, I_D = -7A$	-	37	46	m $\Omega$
		$V_{GS} = -4.5V, I_D = -4A$	-	60	72	
<b>Dynamic Characteristics</b>						
$C_{iss}$	Input Capacitance	$V_{DS} = -15V, V_{GS} = 0V,$ $f = 1.0\text{MHz}$	-	307	-	pF
$C_{oss}$	Output Capacitance		-	60	-	pF
$C_{rss}$	Reverse Transfer Capacitance		-	43	-	pF
$Q_g$	Total Gate Charge	$V_{DS} = -15V, I_D = -4A,$ $V_{GS} = -10V$	-	10	-	nC
$Q_{gs}$	Gate-Source Charge		-	2	-	nC
$Q_{gd}$	Gate-Drain("Miller") Charge		-	2.7	-	nC
<b>Switching Characteristics</b>						
$t_{d(on)}$	Turn-on Delay Time	$V_{DD} = -15V, I_D = -7A,$ $V_{GS} = -10V,$ $R_{GEN} = 2.5\Omega$	-	11	-	ns
$t_r$	Turn-on Rise Time		-	19	-	ns
$t_{d(off)}$	Turn-off Delay Time		-	45	-	ns
$t_f$	Turn-off Fall Time		-	26	-	ns
<b>Drain-Source Diode Characteristics and Maximum Ratings</b>						
$I_S$	Maximum Continuous Drain to Source Diode Forward Current		-	-	-7	A
$I_{SM}$	Maximum Pulsed Drain to Source Diode Forward Current		-	-	-28	A
$V_{SD}$	Drain to Source Diode Forward Voltage	$V_{GS} = 0V, I_S = -7A$	-	-0.8	-1.2	V

Notes:

1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
2.  $E_{AS}$  condition :  $T_J = 25^\circ\text{C}, V_{DD} = -15V, V_G = -10V, L = 0.5\text{mH}, R_g = 25\Omega, I_{AS} = -11A$
3. Pulse Test: Pulse Width  $\leq 300\mu s$ , Duty Cycle  $\leq 0.5\%$



## Test Circuit-N

Figure 1: Gate Charge Test Circuit & Waveform




Figure 2: Resistive Switching Test Circuit & Waveforms







Figure 3: Unclamped Inductive Switching Test Circuit & Waveforms







## Test Circuit-P



### Gate Charge Test Circuit & Waveform





### Resistive Switching Test Circuit & Waveforms



### Unclamped Inductive Switching (UIS) Test Circuit & Waveforms




### Diode Recovery Test Circuit & Waveforms






# Package Mechanical Data

## SOP-8



Dim	Min(mm)	Max(mm)
A	-	1.75
A1	0.10	0.20
A2	1.30	1.50
A3	0.15	0.25
b	0.3	0.5
D	4.85	4.95
E	5.90	6.10
E1	3.85	3.95
e	1.27 Typ	
h	-	0.35
L	0.62	0.82
θ	0°	8°

### suggested Pad Layout



Dimensions	Value(mm)
X	0.60
Y	1.55
C1	5.4
C2	1.27



## Ordering information

Order Code	Package	Channel	V <sub>DS</sub> (V)	I <sub>D</sub> (A)	R <sub>DS(ON)</sub> ( m Ω )	
QN4606C	SOP-8	N-Channel	30	9	V <sub>GS</sub> =10V	< 27
					V <sub>GS</sub> =4.5V	< 37
		P-Channel	-30	-7	V <sub>GS</sub> =-10	< 46
					V <sub>GS</sub> =-4.5	< 72