



REV.	DESCRIPTION	ECN NO.	NAME	DATE

-, MATERIAL:

1. Insulator: PBT+30% Glass Fiber
2. Contact: Brass
3. Contact Plated: Gold Flash over Tin Or Gold Plated Or Tin Plated
4. Shell: Steel, Nickel Plated

=, SPECIFICATION:

1. Current Rating: 5 AMPS
2. Insulation Resistance: 100M Ω MIN. At 500VDC
3. Dielectric Strength: 500V for One minute
4. Operation Temperature: $-55^{\circ}C \sim +105^{\circ}C$.

✳️【胶芯颜色、防火要求、环保要求及电镀规格 依据客户实际订单要求为准】

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD			
DIM.	TOL.	TITLE: DP9F插板柳鱼叉锁螺丝			
x.	± 0.30	DWG. NO.: D-SUB-DS1034-09F		CHECKED: MAX	
x.x	± 0.25	PART NO.: D-SUB-DS1034-09F		DRAWN: ELLA	
x.xx	± 0.15	UNIT: mm		APPROVED: WILL	
GENERAL ANGLE:		SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn
x.	$\pm 5.0^{\circ}$				
x.x'	$\pm 2.0^{\circ}$				
x.xx'	$\pm 1.0^{\circ}$				

BXCONN[®]

