








**ELECTRICAL CHARACTERISTICS** ( $T_j=25^\circ\text{C}$  unless otherwise specified)

Symbol	Test Condition	Value		Unit
$I_{GT}$	$V_D=12\text{V } R_L=100\Omega$	MAX.	15	mA
$V_{GT}$		MAX.	1.5	V
$V_{GD}$	$V_D=V_{DRM} T_j=125^\circ\text{C } R_L=100\Omega$	MIN.	0.2	V
$I_L$	$I_G=1.2I_{GT}$	MAX.	40	mA
			60	
$I_H$	$I_T=500\text{mA}$	MAX.	30	mA
$dV/dt$	$V_D=2/3V_{DRM} T_j=125^\circ\text{C}$	MIN.	500	V/ $\mu\text{s}$

**STATIC CHARACTERISTICS**

Symbol	Parameter		Value(MAX.)	Unit
$V_{TM}$	$I_{TM}=32\text{A}$	$T_j=25^\circ\text{C}$	1.75	V
$V_{TO}$	Threshold voltage	$T_j=125^\circ\text{C}$	0.86	V
$R_D$	Dynamic resistance	$T_j=125^\circ\text{C}$	36.6	m $\Omega$
$I_{DRM}$	$V_D=V_{DRM} V_R=V_{RRM}$	$T_j=25^\circ\text{C}$	5	$\mu\text{A}$
$I_{RRM}$		$T_j=125^\circ\text{C}$	1	mA

## TYPICAL CHARACTERISTICS

**FIG.1** Maximum power dissipation versus RMS on-state current

**FIG.2:** RMS on-state current versus case temperature

**FIG.3:** Surge peak on-state current versus number of cycles

**FIG.5:** Non-repetitive surge peak on-state current for a sinusoidal pulse with width  $t_p < 10\text{ms}$ , and corresponding value of  $I^2t$  ( $di/dt < 100\text{A}/\mu\text{s}$ )

**FIG.4:** On-state characteristics

**FIG.6:** Relative variations of gate trigger current, holding current and latching current versus junction temperature
