




| REV. | EC# | DESCRIPTION | DATE DRAWN | CHECK | APPROVED |
|------|-----|-------------|------------|-------|----------|
| 1.00 |     | 初版发行        | 2020-8-28  |       |          |
|      |     |             |            |       |          |
|      |     |             |            |       |          |

|       |       |       |       |
|-------|-------|-------|-------|
| 2x15P | 32.0  | 28.0  | 30.9  |
| 2x14P | 30.0  | 26.0  | 28.9  |
| 2x13P | 28.0  | 24.0  | 26.9  |
| 2x12P | 26.0  | 22.0  | 24.9  |
| 2x11P | 24.0  | 20.0  | 22.9  |
| 2x10P | 22.0  | 18.0  | 20.9  |
| 2x9P  | 20.0  | 16.0  | 18.9  |
| 2x8P  | 18.0  | 14.0  | 16.9  |
| 2x7P  | 16.0  | 12.0  | 14.9  |
| 2x6P  | 14.0  | 10.0  | 12.9  |
| 2x5P  | 12.0  | 8.0   | 10.9  |
| 2x4P  | 10.0  | 6.0   | 8.9   |
| 2x3P  | 8.0   | 4.0   | 6.9   |
| 2x2P  | 6.0   | 2.0   | 4.9   |
| PIN   | DIM.A | DIM.B | DIM.C |

技术要求:

- 1) 材质: 见附表;
- 2) 电镀: 见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

温度范围: -25°C~85°C  
额定电压: 250V AC/DC  
额定电流: 3A AC/DC  
接触电阻: ≤0.02Ω  
绝缘电阻: ≥1000MΩ  
耐压值: 800V AC/minute  
适用基板厚度: 1.6mm

|     |         |       |                              |
|-----|---------|-------|------------------------------|
| 2   | PIN     | n PCS | 材质: 黄铜, 电镀: 镀亮锡              |
| 1   | Housing | 1 PCS | 材质: PA6T (耐温UL94V-0), 颜色: 米色 |
| NO. | NAME    | Q'TY  | DESCRIPTION                  |



深圳市韩下电子有限公司

|                  |     |           |         |             |            |             |
|------------------|-----|-----------|---------|-------------|------------|-------------|
| DRAW:            | 黄彬  | 2020-8-28 | TITLE:  | 针座          | DRAW NAME: | HX-PHB-2x5A |
| DESIGN:          |     |           | SERIES: | PHSD SERIES | DRAW NO.   |             |
| CHECK:           | 张伟  | 2020-8-28 | P/N:    |             | UNIT:      | mm          |
| APPROVED         | 罗小春 | 2020-8-28 | REV.    | 1.00        | SHEET:     | 1/1         |
| CUSTOMER DRAWING |     |           | SCALE   | N/A         |            |             |

| GENERAL TOLERANCES |       |        |        |
|--------------------|-------|--------|--------|
| DIM                | TOL   | DIM    | DEG    |
| X.                 |       | X°     | ±3.00° |
| X.X                | ±0.35 | X.X°   | ±2.00° |
| X.XX               | ±0.25 | X.XX°  | ±1.00° |
| X.XXX              | ±0.15 | X.XXX° |        |