

■ **Features**

- Glass passivated chip
- Low reverse leakage current
- High surge current capability
- Reliable low cost construction utilizing molded plastic technique


Reverse Voltage 600 V
Forward Current 15.0 A max

■ **Applications**

- General purpose use in AC/DC bridge full wave rectification

■ **Mechanical Data**

- Case: GBU
- Polarity symbols being marked on body
- Molding compound meets UL 94V-0 flammability rating
- RoHS-compliant, Solder plated, solderable per MIL-STD-750, Method 2026



■ **Marking**

- GBU1506L

■ **Maximum Ratings @ Ta = 25°C unless otherwise noted**

PARAMETER	SYMBOL	UNIT	GBU1506L
Repetitive peak reverse voltage	V_{RRM}	V	600
Maximum RMS voltage	V_{RMS}	V	420
Maximum DC blocking Voltage	V_{DC}	V	600
Maximum average output current@60Hz sine wave, resistance load	$I_{F(AV)}$	A	15.0
Peak forward surge current 8.3 ms single half sine wave superimposed on rated load	I_{FSM}	A	300
Peak forward surge current 1.0 ms single half sine wave superimposed on rated load		A	600
Current squared time @1ms≤t<8.3ms Tj=25°C, Rating of per diode	I^2t	A²S	373.50
Storage temperature	T_{stg}	°C	-55~+150
Junction temperature	T_j	°C	-55~+150

■ **Electrical Characteristics @ Ta = 25°C unless otherwise noted**

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	GBU1506L
Maximum instantaneous forward voltage	$I_F=7.5A$	V_F	V	0.92
Maximum DC reverse current at rated DC blocking voltage	$V_R=V_{DC}, T_j=25°C$	I_R	μA	5
	$V_R=V_{DC}, T_j=100°C$	I_R		500

■ Characteristic Curve (Typical)




FIG1. Derating Curve For Output Rectified Current




FIG2. Surge Forward Current Capability




FIG3. Typical Forward Characteristics





FIG4. Typical Reverse Characteristics

■ **Marking and packet information**




GBU**** : Marking Model

TQS : Brand Logo

Packaging information	
每盒	500PCS
每箱	5000PCS
脚长定制	支持

■ **GBU Package outline dimensions**



Dimensions in millimeters

■ **Notice**

XILONG reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to any product herein. xilong does not assume any liability arising out of the application or use of any product described herein.