






REVISIONS			
REV.	ECN, ERN NO.	DATE	APPROVED
A	PROPOSAL DRAWING	AUG12/14	L.CHAN
B	ADD A VIEW TO SHOW KAPTON POSITION	SEP01/14	L.CHAN
C	DRAWING REVISED	NOV21/14	L.CHAN



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)



RECOMMENDED PANEL CUTOUT

1.MATERIALS:
HOUSING: HIGH TEMPERATURE THERMOPLASTIC,
FLAMMABILITY RATING UL 94V-0,
COLOR: BLACK

CONTACT: PHOSPHOR BRONZE
PLATING: SELECTIVELY PLATED GOLD REFER TO PART
NUMBER OPTIONS ON MATING SURFACE.
50 U" MIN. NICKEL OVERALL
100 U" MIN. BRIGHT TIN OR
GOLD FLASH ON CONTACT TAILS.

HOLD DOWN: COPPER ALLOY PLATED WITH BRIGHT TIN,
SHIELDED: BRASS WITH NICKEL PLATED

2.COPLANARITY SPECIFICATION:
WITH THE MODULAR JACK SITTING ON A LEVEL SURFACE, THE
MAXIMUM GAP BETWEEN THE LEVEL SURFACE AND ALL TERMINAL
TAILS AND BOTH FITTING NAILS IS 0.10 [.004].

PART NUMBER: RJE23-188-1X17-T

GOLD PLATING

1 = 6u" INCH
2 = 15u" INCH
3 = 30u" INCH
4 = 50u" INCH

UNLESS SPECIFIED OTHERWISE	DRAWN J.FENG	AUG12/14
PRIMARY UNITS MILLIMETERS	CHECKED L.CHAN	AUG12/14
SECONDARY INCHES	M.E. APP'D	
REFERENCE IN PARENTHESES	Q.A. APP'D	
GENERAL TOLERANCES	DWG APP'D	
1 DECIMAL PLACE ±0.38	ENG. REL. NO.	
2 DECIMAL PLACES ±0.25	REF.	
3 DECIMAL PLACES ±0.13	THIRD ANGLE PROJECTION	
ANGULAR DEGREES ±3°	DO NOT SCALE DRAWING	

Amphenol Canada Corp.

TITLE SINGLE-PORT MODULAR JACK, TOP ENTRY,
8 POSITIONS, 8 CONTACTS, SURFACE MOUNT,
SHIELDED, WITH KAPTON, T&R PACKAGE
-RoHS COMPLIANT





DWG NO. P-RJE23-188-1X17-T

REV C

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

CODE ID NO. 03554 DWG SIZE C SCALE N/A SHEET 1 OF 2

REVISIONS			
REV.	ECN, ERN NO.	DATE	APPROVED
A	PROPOSAL DRAWING	AUG12/14	L.CHAN
B	ADD A VIEW TO SHOW KAPTON POSOTION	SEP01/14	L.CHAN
C	DRAWING REVISED	NOV21/14	L.CHAN



- PACKAGING NOTES:
1. ONE REEL SHOULD HOLD 120 CONNECTORS.
 2. 5 EMPTY CAVITIES FOR CARRIER TAPE LEADER & 5 EMPTY CAVITIES FOR CARRIER TAPE TRAILER.
 3. A FULLY LOADED CARTON SHOULD CONTAIN 5 REELS(600 PCS) OF CONNECTORS.

UNLESS SPECIFIED OTHERWISE		DRAWN	J.FENG	AUG12/14	Amphenol Canada Corp.	
PRIMARY UNITS	MILLIMETERS	CHECKED	L.CHAN	AUG12/14		
SECONDARY	INCHES	M.E. APP'D			TITLE	
REFERENCE IN PARENTHESES		Q.A. APP'D				
GENERAL TOLERANCES		DWG APP'D			SINGLE-PORT MODULAR JACK, TOP ENTRY, 8 POSITIONS, 8 CONTACTS, SURFACE MOUNT, SHIELDED, WITH KAPTON, T&R PACKAGE -RoHS COMPLIANT	
1 DECIMAL PLACE	±0.38	ENG. REL. NO.				
2 DECIMAL PLACES	±0.25	REF.			DWG NO. P-RJE23-188-1X17-T	
3 DECIMAL PLACES	±0.13	THIRD ANGLE PROJECTION				
ANGULAR DEGREES	±3°	DO NOT SCALE DRAWING			CODE ID NO. 03554	DWG SIZE C SCALE N/A SHEET 2 OF 2

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.