



General Description

The HSH120P03 is the high cell density trench P-ch MOSFETs, which provide excellent RDSON and gate charge for most of the synchronous buck converter applications.

The HSH120P03 meet the RoHS and Green Product requirement, 100% EAS guaranteed with full function reliability approved.


Product Summary

V_{DS}	-30	V
$R_{DS(ON),typ}$	3.5	m Ω
I_D	-120	A

Features

- Super Low Gate Charge
- 100% EAS Guaranteed
- Green Device Available
- Excellent CdV/dt effect decline
- Advanced high cell density Trench Technology

TO-263 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	-30	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_C=25^{\circ}C$	Continuous Drain Current, V_{GS} @ -10V ^{1,6}	-120	A
$I_D@T_C=100^{\circ}C$	Continuous Drain Current, V_{GS} @ -10V ^{1,6}	-89	A
I_{DM}	Pulsed Drain Current ²	-504	A
EAS	Single Pulse Avalanche Energy ³	576	mJ
$P_D@T_C=25^{\circ}C$	Total Power Dissipation ⁴	200	W
T_{STG}	Storage Temperature Range	-55 to 150	$^{\circ}C$
T_J	Operating Junction Temperature Range	-55 to 150	$^{\circ}C$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient ¹ (Steady State)	---	62	$^{\circ}C/W$
$R_{\theta JC}$	Thermal Resistance Junction-case ¹	---	0.81	$^{\circ}C/W$



Electrical Characteristics ($T_J=25^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=-250\mu A$	-30	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance ²	$V_{GS}=-10V, I_D=-20A$	---	3.5	3.9	$m\Omega$
		$V_{GS}=-4.5V, I_D=-20A$	---	5.1	6	$m\Omega$
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}, I_D=-250\mu A$	-1.0	-1.6	-2.5	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=-24V, V_{GS}=0V, T_J=25^\circ\text{C}$	---	---	-1	μA
		$V_{DS}=-24V, V_{GS}=0V, T_J=55^\circ\text{C}$	---	---	-5	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0V$	---	---	± 100	nA
Q_g	Total Gate Charge (-10V)	$V_{DS}=-15V, V_{GS}=-10V, I_D=-20A$	---	125	---	nC
Q_{gs}	Gate-Source Charge		---	12	---	
Q_{gd}	Gate-Drain Charge		---	31	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=-15V, V_{GS}=-10V, R_G=3.3\Omega, I_D=-20A$	---	14	---	ns
T_r	Rise Time		---	12	---	
$T_{d(off)}$	Turn-Off Delay Time		---	66	---	
T_f	Fall Time		---	35	---	
C_{iss}	Input Capacitance	$V_{DS}=-15V, V_{GS}=0V, f=1\text{MHz}$	---	7300	---	pF
C_{oss}	Output Capacitance		---	819	---	
C_{rss}	Reverse Transfer Capacitance		---	530	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current ^{1,5}	$V_G=V_D=0V$, Force Current	---	---	-120	A
V_{SD}	Diode Forward Voltage ²	$V_{GS}=0V, I_S=-1A, T_J=25^\circ\text{C}$	---	---	-1.2	V

Note :

- 1.The data tested by surface mounted on a 1 inch²FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$
- 3.The EAS data shows Max. rating . The test condition is $V_{DD}=-15V, V_{GS}=-10V, L=0.5mH, R_g=25R$
- 4.The power dissipation is limited by 150°C junction temperature
- 5.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation
- 6.The maximum current rating is package limited.



Typical Characteristics




Fig.1 Typical Output Characteristics




Fig.2 Transfer Characteristics




Fig.3 Power Dissipation




Fig.4 Drain Current




Fig.5 BV_{DSS} vs Junction Temperature




Fig.6 $R_{DS(ON)}$ vs Junction Temperature




Fig.7 Gate Charge Waveforms




Fig.8 Capacitance




Fig.9 Body Diode Characteristics





Fig.10 Maximum Safe Operating Area



Ordering Information

Part Number	Package code	Packaging
HSH120P03	TO-263	800/Tape&Reel

TO-263 Package Outline



COMMON DIMENSIONS(UNIT OF MEASURE - MM)

SYMBOL	MIN	NOM	MAX
A	4.37	4.57	4.77
A1	0.00	-	0.25
b	0.70	0.83	0.96
b1	1.00	1.24	1.47
C	0.35	0.45	0.55
C1	1.25	1.30	1.35
D	8.50	8.90	9.30
D1	7.50	8.00	8.50
H	14.7	15.20	15.7
E	9.80	10.08	10.4
E1	7.35	7.80	8.25
e1	4.93	5.08	5.23
L	2.00	2.30	2.60
L1	4.50	4.75	5.00
L2	1.30	1.53	1.75
L3	1.10	1.29	1.47
e	2.54 BSC		
θ	13°TYP		



HSH120P03 Marking:

