

TO-252 Plastic-Encapsulate MOSFETS

Features

- $V_{DS}=60V$
- $I_D=50A$
- $R_{DS(on)}@V_{GS}=10V < 15m\Omega$
- $R_{DS(on)}@V_{GS}=4.5V < 21m\Omega$
- Fast Switching
- Low Gate Charge and R_{dson}
- Advancedz Trench Technology

Drain-source Voltage
60 V
Drain Current
50 Ampere


Applications

- DC-DC Converters
- PWM application
- Power management

Mechanical Data

- Case: TO-252
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant,halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram



Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
TO-252	R3	0.305	2500	5000	25000	13"

Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Drain-source Voltage	V_{DS}	V	60
Gate-source Voltage	V_{GS}	V	± 20
Drain Current	I_D	A	50
Pulsed Drain Current ⁽¹⁾	I_{DM}	A	200
Total Power Dissipation	P_D	W	62.5
Single pulse avalanche energy ⁽²⁾	EAS	mJ	72
Junction temperature	T_J	°C	150
Storage temperature	T_{stg}	°C	-55 ~+150
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	°C / W	2

● Static Parameter Characteristics (Tj=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} = 0V, I _D =250μA	V	60	—	—
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =60V, V _{GS} =0V	μA	—	—	1.0
Gate-Body Leakage Current	I _{GSS}	V _{GS} = ±20V, V _{DS} =0V	nA	—	—	±100
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D =250μA	V	1.0	1.5	2.5
Static Drain-Source On-Resistance ⁽³⁾	R _{DS(on)}	V _{GS} = 10V, I _D =30A	mΩ	—	11	15
		V _{GS} = 4.5V, I _D =20A		—	13.5	21

● Dynamic Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Input Capacitance	C _{iss}	V _{DS} =25V, V _{GS} =0V, f=1MHZ	pF	—	1985	—
Output Capacitance	C _{oss}			—	136	—
Reverse Transfer Capacitance	C _{rss}			—	124	—

● Switching Parameters







PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Turn-on Delay Time	t _{D(on)}	V _{GS} =10V, V _{DD} =30V, I _D =30A, R _{GEN} =1.8Ω	nS	—	11	—
Turn-on Rise Time	t _r		nS	—	79	—
Turn-off Delay Time	t _{D(off)}		nS	—	33	—
Turn-off fall Time	t _f		nS	—	107	—
Total Gate Charge	Q _g	V _{DS} =30V, I _D =30A V _{GS} =10V	nC	—	45	—
Gate-Source Charge	Q _{gs}		nC	—	8	—
Gate-Drain Charge	Q _{gd}		nC	—	11	—

● Drian-Source Diode Characteristics





PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Diode Forward Voltage	V _{SD}	I _S =50A, V _{GS} =0V	V	—	—	1.2
Maximum Body-Diode Continuous Current	I _S	—	A	—	—	50

Note :
(1)Repetitive Rating: Pulse width limited by maximum junction temperature.
(2)EAS condition : Tj=25°C ,VDD=30V,VG=10V,L=0.5mH,IAS=17A,Rg=25Ω.
(3)Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 0.5%.

● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Package Outline Dimensions (TO-252)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A2	0.90	1.10	0.035	0.043
b	0.66	0.86	0.026	0.034
b1	5.10	5.46	0.201	0.215
b2	4.27	4.37	0.168	0.172
b3	0.78	0.90	0.031	0.035
c	0.46	0.58	0.018	0.023
D	6.00	6.20	0.236	0.244
D1	5.35 REF.		0.211 REF.	
E	6.50	6.70	0.256	0.264
E1	4.83 REF.		0.190 REF.	
e	2.18	2.38	0.086	0.094
H	9.80	10.4	0.386	0.409
L1	2.90 REF.		0.114 REF.	
L3	0.90	1.20	0.035	0.047
L4	0.60	1.00	0.024	0.039
L5	1.6 REF.		0.063 REF.	
L6	-	0.12	-	0.005

● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
a	3.70	-	0.146	-
b	4.37	-	0.172	-
X	-	5.80	-	0.228
X1	-	1.20	-	0.047
Y	-	5.85	-	0.230
Y1	-	2.00	-	0.079


1. Gate Charge Test Circuit & Waveforms



2. Resistive Switching Test Circuit & Waveforms



3. Unclamped Inductive Switching (UIS) Test Circuit & Waveforms



4. Diode Recovery Test Circuit & Waveforms

