

General Description

The HSM1564 is the high cell density trench N-ch MOSFETs, which provide excellent RDSON and gate charge for most of the synchronous buck converter applications.

The HSM1564 meet the RoHS and Green Product requirement, 100% EAS guaranteed with full function reliability approved.


Features

- 100% EAS Guaranteed
- Green Device Available
- Super Low Gate Charge
- Excellent CdV/dt effect decline
- Advanced high cell density Trench Technology

Product Summary

V_{DS}	60	V
$R_{DS(ON),TYP}$	13.5	mΩ
I_D	8	A

Dual SOP8 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	60	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_A=25^{\circ}C$	Continuous Drain Current, V_{GS} @ 10V	8	A
$I_D@T_A=70^{\circ}C$	Continuous Drain Current, V_{GS} @ 10V	6	A
I_{DM}	Pulsed Drain Current ¹	32	A
EAS	Single Pulse Avalanche Energy ²	150	mJ
$P_D@T_A=25^{\circ}C$	Total Power Dissipation	2	W
T_{STG}	Storage Temperature Range	-55 to 150	$^{\circ}C$
T_J	Operating Junction Temperature Range	-55 to 150	$^{\circ}C$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-Ambient	---	75	$^{\circ}C/W$



Electrical Characteristics ($T_J=25^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	60	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance ²	$V_{GS}=10V, I_D=20A$	---	13.5	17	$m\Omega$
		$V_{GS}=4.5V, I_D=15A$	---	15.5	20	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}, I_D=250\mu A$	1.0	1.5	2.5	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=60V, V_{GS}=0V, T_J=25^\circ\text{C}$	---	---	1	μA
		$V_{DS}=60V, V_{GS}=0V, T_J=125^\circ\text{C}$	---	---	500	nA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=5V, I_D=20A$	---	35	---	S
R_g	Gate Resistance	$V_{DS}=0V, V_{GS}=0V, f=1\text{MHz}$	---	1.4	---	Ω
Q_g	Total Gate Charge	$V_{DS}=30V, V_{GS}=10V, I_D=20A$	---	47.5	---	nC
Q_{gs}	Gate-Source Charge		---	14.5	---	
Q_{gd}	Gate-Drain Charge		---	12.7	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=30V, V_{GS}=10V, R_G=6\Omega, R_L=1.5\Omega$	---	4.3	---	ns
T_r	Rise Time		---	16	---	
$T_{d(off)}$	Turn-Off Delay Time		---	6.5	---	
T_f	Fall Time		---	24	---	
C_{iss}	Input Capacitance	$V_{DS}=30V, V_{GS}=0V, f=1\text{MHz}$	---	2411	---	pF
C_{oss}	Output Capacitance		---	124	---	
C_{rss}	Reverse Transfer Capacitance		---	116	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current(Body Diode)	$V_G=V_D=0V$, Force Current	---	---	9.5	A
V_{SD}	Diode Forward Voltage ³	$V_{GS}=0V, I_S=20A, T_J=25^\circ\text{C}$	---	---	0.99	V
T_{rr}	Reverse Recovery Time	$I_F=20A, dI/dt=100A/\mu s$	---	24	---	ns
Q_{rr}	Reverse Recover Charge	$I_F=20A, dI/dt=100A/\mu s$	---	9.3	---	nC

Note :

1.Repetitive Rating : Plused width limited by maximum junction temperature.

2.EAS condition : $T_J=25^\circ\text{C}$, $V_{DD}=40V$, $V_G=10V$, $R_g=25\Omega$, $L=0.5mH$

3.Repetitive Rating : Plused width limited by maximum junction temperature.



Typical Characteristics




Figure 1. Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. Power Dissipation




Figure 4. Drain Current




Figure 5. BV_{DS} vs Junction Temperature




Figure 6. R_{DS(ON)} vs Junction Temperature



Dual N-Ch 60V Fast Switching MOSFETs




Figure 7. Gate Charge Waveforms




Figure 8. Capacitance




Figure 9. Body-Diode Characteristics





Figure 10. Maximum Safe Operating Area



Ordering Information

Part Number	Package code	Packaging
HSM1564	SOP-8	2500/Tape&Reel

SOP-8 Package Outline



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
C	0.170	0.250	0.007	0.010
D	4.800	5.000	0.189	0.197
e	1.270 (BSC)		0.050(BSC)	
E	5.800	6.200	0.228	0.244
E1	3.800	4.000	0.150	0.157
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°

HSM1564 Marking:

