

General Description

The CMSC4963 uses advanced trench technology to provide excellent RDS(ON). It is a suitable device for most synchronous buck converter applications.


Product Summary

BVDSS	R _{DS(on)} max.	ID
-20V	26mΩ	-10A

Applications

- DC/DC Conversion
- Load Switches

DFN-8 3.3x3.3 Pin Configuration



Features

- Dual P-Channel MOSFET
- Low ON-resistance
- Surface Mount Package
- RoHS Compliant

Type	Package	Marking
CMSC4963	DFN-8 3.3x3.3	4963

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V _{DS}	Drain-Source Voltage	-20	V
V _{GS}	Gate-Source Voltage	±12	V
I _D @T _C =25°C	Continuous Drain Current	-10	A
I _D @T _C =100°C	Continuous Drain Current	-7	A
I _{DM}	Pulsed Drain Current	-40	A
EAS	Single Pulse Avalanche Energy ¹	24	mJ
P _D @T _C =25°C	Total Power Dissipation	20	W
T _{STG}	Storage Temperature Range	-55 to 150	°C
T _J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R _{θJA}	Thermal Resistance Junction-ambient	---	78	°C/W
R _{θJC}	Thermal Resistance Junction-case	---	6.25	°C/W

Electrical Characteristics (T_J=25°C , unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V , I _D =-250μA	-20	---	---	V
R _{DS(ON)}	Static Drain-Source On-Resistance	V _{GS} =-4.5V , I _D =-3.7A	---	22	26	mΩ
		V _{GS} =-2.5V , I _D =-2A	---	27	35	
V _{GS(th)}	Gate Threshold Voltage	V _{GS} =V _{DS} , I _D = -250μA	-0.4	---	-1.0	V
I _{DSS}	Drain-Source Leakage Current	V _{DS} =-20V , V _{GS} =0V	---	---	-1	μA
I _{GSS}	Gate-Source Leakage Current	V _{GS} =±12V , V _{DS} =0V	---	---	±100	nA
g _{fs}	Forward Transconductance	V _{DS} =-5V , I _D =-2A	---	9	---	S
R _g	Gate Resistance	V _{DS} =0V , V _{GS} =0V , f=1MHz	---	8	---	Ω
Q _g	Total Gate Charge	V _{DS} =-10V , I _D =-7A V _{GS} =-4.5V (Note 2)	---	13	---	nC
Q _{gs}	Gate-Source Charge		---	2	---	
Q _{gd}	Gate-Drain Charge		---	3.4	---	
T _{d(on)}	Turn-On Delay Time	V _{DD} =-10V , V _{GS} =-4.5V R _L =-1.43Ω , R _{GEN} =3Ω (Note 2)	---	10	---	ns
T _r	Rise Time		---	15	---	
T _{d(off)}	Turn-Off Delay Time		---	85	---	
T _f	Fall Time		---	40	---	
C _{iss}	Input Capacitance	V _{DS} =-10V , V _{GS} =0V , f=1MHz	---	1030	---	pF
C _{oss}	Output Capacitance		---	150	---	
C _{rss}	Reverse Transfer Capacitance		---	120	---	

Diode Characteristics







Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I _S	Continuous Source Current	V _G =V _D =0V , Force Current	---	---	-10	A
I _{SM}	Pulsed Source Current		---	---	-40	A
V _{SD}	Diode Forward Voltage	V _{GS} =0V , I _S =-5A , T _J =25°C	---	-0.87	-1.2	V


Note :

- The EAS data shows Max. rating . The test condition is V_{DD}=-15V , V_{GS}=-10V , L=0.3mH , I_{AS}=-12.8A.
- Defined by design, not subject to production.

This product has been designed and qualified for the consumer market.
Cmos assumes no liability for customers' product design or applications.
Cmos reserves the right to improve product design ,functions and reliability without notice.Please refer to the latest version of specification.

Typical Characteristics



Package Dimension
DFN-8 3.3X3.3 Dual
Unit :mm


Dimensions In Millimeters			
Symbol	Min.	Max.	Ave.
A	0.700	0.900	0.800
D	3.000	3.200	3.100
E	3.000	3.200	3.100
E1	3.200	3.600	3.400
b	0.200	0.400	0.300
e	0.550	0.750	0.650
L	0.250	0.650	0.450
L1	0.255	0.655	0.455
L2	0.935	1.135	1.035

Note:

1. No tolerance ± 0.10
2. The plastic package has no defects such as defects, shrinkage holes, cracks, bubbles, etc.
3. Marking unit mm