





7	8	9	10
版本	变更原因与内容	日期	变更者
A	INITIAL REALSE	23-12-29	
B			






SECT: X-X  
比例 4.000




OPEN SITUATION

- NOTES:
- MATERIAL:  
HOUSING: LCP,UL 94V-0,COLOR:BLACK;  
COVER: LCP,UL 94V-0,COLOR:NATURE;  
CONTACT: PHOSPOR BRONZE;  
PEG: BRASS;
  - PLATING:  
CONTACT: 80u" MIN. NICKEL PLATED OVERALL;  
GOLD PLATED ON CONTACT AREA;  
1u" Au PLATED ON SOLDER TAIL AREA  
PEG: 120-200u" TIN PLATED ON NICKEL OVERAL
  - RATING:  
CURRENT RATING: 0.4A AC/DC  
VOLTAGE RATING: 50V AC/DC
  - PART NO.(P/N):



RECOMMEND FFC/FPC SCALE:5:1



FFC/FPC INSERT DIRECTION  
RECOMMEND PCB LAYOUT  
SCALE:5:1

PTN NO.	DTM.A	DTM.B	DTM.C
40	15.6	21.2	19.7
60	23.6	29.2	27.7
80	31.6	37.2	35.7
90	35.6	41.2	39.7
100	39.6	45.2	43.7
120	47.6	53.2	51.7

<b>HSF STD</b>		<b>深圳市文章济美科技有限公司</b>			
 <b>GP</b>	 <b>HF</b>	常规公差表示			
		0.000	±0.10	0.00°	±0.05°
		0.00	±0.15	0.0°	±0.2°
		0.0	±0.20	0°	±0.5°
0.	±0.30				
无特殊情况,以常规公差为准;若图面上有公差表示时,以图面公差为准.图面公制单位(mm)		核准: PJJ	品名: 0.4PITCH,2.5HFPC EASY-ON R/A SMT TYPE.		
		审核: HHK	料号: 5001-FPC0425-**R1-00-B		
		设计: PENGJINYA	页数: 01 OF 01		
			SIZE 版本: A4 A		