



NOTES:

备注

1. Brass or purple copper, tin-plating
黄铜或紫铜, 镀锡
2. Wire screw hole M5
压线螺孔M5
3. Current Rating: 60A
额定电流: 60A
4. The maximum torque of the screw hole: 2.03 N/m
螺孔最大扭力: 2.03 N/m
5. Operating Temperature: -40°C~+125°C
工作温度: -40°C~+125°C
6. Has passed the 72 hour salt spray test
已通过72小时盐雾测试
7. There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
8. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差

Ordering Information

HC - * ** * * - **** - D *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	DIP	Product No.	Material
W-hill Tooth (插子)	08=0.8mm	3=M3 (螺母)	2=2个	0808=8x8mm	I=SIP	产品序号	默认=Copper (黄铜)
RN=Rivet Nut (铆螺母)	10=1.0mm	4=M4 (螺母)	4=4个	1620=16x20mm	S=SMT		BC=Red Copper (紫铜)
RG=Rivet Gasket (铆垫片)	12=1.2mm	5=M5 (螺母)	4=4个	FD=Flag Dip		
	15=1.5mm	6=M6 (螺母)	6=6个				
	20=2.0mm	25=2.5mm	8=8个				
	30=3.0mm	32=3.2mm					

			GENEAL TOLERANCE	制图 DRAWING	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审核 CHECK		产品名称 TITLE	PCB 焊接端子 厚度1.0 插板 铆垫片 M5 4焊脚 11x10x10.5mm	版本 REV.	A
			5 or more ±0.35	批准 APPROVAL		产品料号 PART NO.	HC-RG1054-1110-D329-07	单位 UNITS	mm
1	初版发行		2~5 ±0.25	比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	0~2 ±0.15	投影 Projection					
			Angle ±3.0°						