




NOTES:

备注

1. Copper, Bright tin plated
黄铜, 镀亮镍
2. Wire screw hole M4
压线螺孔M4
3. Current Rating: 45A
额定电流: 45A
4. There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
5. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



PCB 参考安装方式

Ordering Information

HC - * ** * - **** - * ** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	ImpP	Product No.	Material
0#=1.0mm (0号)	0#=1.0mm (0号)	0#=0 (螺牙)	0#=0 (焊脚)	1620#16x20mm	0#=1mm Dip	产品序号	默认Copper (黄铜)
1#=1.2mm (1号)	1#=1.2mm (1号)	1#=0.8 (螺牙)	1#=0.8 (焊脚)
2#=1.5mm (2号)	2#=1.5mm (2号)	2#=0.8 (螺牙)	2#=0.8 (焊脚)
3#=2.0mm (3号)	3#=2.0mm (3号)	3#=0.8 (螺牙)	3#=0.8 (焊脚)

		GENREL TOLERANCE		制图	07		
		DIM	TOL	审核	深圳市华灿天禄电子有限公司		
		5 or more	±0.35	CHECK	ShenzhenhuacantianluELECTRONICS CO.,LTD		
		2~5	±0.25	批准	产品名称	PCB 焊接端子 厚度0.8 插板 铆垫片	版本
		0~2	±0.15	APPROVAL	TITLE	M4 4焊脚 8x8x8.7mm	REV.
1	初版发行			比例	产品料号	HC-RG0844-0808-D201-07	A
序号	变更内容	日期		SCALE	PART NO.		单位
No.	MODIFY CONTENT	MODIFY DATE		投影	MATERIAL		UNITS
			Angle ±3.0°	Projection			mm
							页次
							SHEET
							1/1