



NOTES:  
备注

- Brass or purple copper, Bright tin-plating  
黄铜或紫铜, 镀亮锡
- Wire screw hole M5  
压线螺孔M5
- Current Rating: 70A  
额定电流:70A
- There shall be no defects such as pin deformation and burrs.  
不得有脚变形, 毛刺等缺陷
- Unmarked dimensions refer to tolerances  
未标注的尺寸参考公差

**Ordering Information**

HC - \* \* \* \* - \* \* \* \* - 07

Type	Thickness	Screw Thread	Welding Feet	Series	D=DF	Product No.	Material
M-Pull Teeth (抽牙)	08=0.8mm	3=M3 (螺牙)	4=M4 (螺牙)	0808=8x8mm	S=SMT	产品序号	默认=Copper (黄铜)
W-Rivet Nut (铆螺母)	10=1.0mm	4=M4 (螺牙)	2=2个	1620=16x20mm	FP=Flag Dip		BC=Red Copper (紫铜)
Rivet (铆钉)	15=1.5mm	5=M5 (螺牙)	4=4个	.....			
W-Rivet Gasket (铆垫片)	20=2.0mm	6=M6 (螺牙)	6=6个				
	25=2.5mm		8=8个				
	30=3.0mm		.....				
	32=3.2mm						

			GENEAL TOLERANCE	制图	07	<b>深圳市华灿天禄电子有限公司</b> ShenzhenhuaciantianluELECTRONICS CO.,LTD				
			DIM TOL	审核						
			5 or more ±0.35	批准		产品名称	PCB 焊接端子 厚度1.2 贴片 抽牙		版本	A
			2~5 ±0.25	APPROVAL		TITLE	M5 4焊脚 30x10x7.9mm		REV.	
			0~2 ±0.15	比例		产品料号	HC-M1254-3010-S525-07		单位	mm
			Angle ±3.0°	投影		PART NO.			页次	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE		材料		MATERIAL			SHEET	