






1		2		3		4		5		6		7		8			
SAMZO		REAC/ROHS								REV	ECN NO	DESCRIPTION	DESIGN	APPROVAL	DATE		
										A1	NEW	Replace frame			2018.06.12		
E		技术要求: Technical requirements:															
E		1. 打铜底0.5-1UM, 镍底1-3UM, 哑锡3-5UM。 Copper base 0.5 - 1 UM, nickel base 1-3UM, matte tin 3 - 5 UM.															
E		2. 不得有脚变形, 毛刺等缺陷。 There shall be no defects such as pin deformation and burrs.															
E		3. 插脚尖部符合可焊性要求。 The tip of the insertion pin shall meet the solderability requirements.															
E		4. 螺纹需符合通止规要求。 The thread shall meet the requirements of the go and no-go gauge.															
D		5. 材质: 黄铜H62。 Material: Brass H62.															
D		6. 过载电流: 60A Overload current: 60A															
D		7. 螺孔为 M4 The screw holes M4															
D		8. 未标注尺寸公差值按GB/T1184-1996H级 Unmarked dimensional tolerance values are in accordance with Grade H of GB/T1184-1996															
C		9. 螺丝扭力: 2.5Nm Screw torque: 2.5Nm															
C																	
B		108 100 35 1 D4															
B				Pressing hole specification: M4													
B				Mold number: C039-H													
B				Pin height: 3.5mm													
B				Height above the board: 10.0mm													
B				Specification size: 10*8mm													
A										FIRST VIEW				TITLE::			
A		ITEM DESCRIPTION MATERIAL QTY FINISH/COLOR										The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM		10*8-H10.0+3.5mm (M4)			
A		A Subject H62(Y2) 1 tin plating								SCALE 1:1 UNIT mm				DWG NO: 108-P034			
A		B Gasket SPCC 1 tin plating				GENERAL TOLERANCE								PART NO: 108-2018101			
A						≥0~2< ±0.15								MODEL NO: 108100351D4			
A				DESIGN WANGGUIFA 2018.06.12		≥2~5< ±0.25				SAMZO COMPONENTS				NAME:			
A				CHECKED ZHENGUILAN 2018.06.12		≥0~2< ±0.15				Electronic switch and connector manufacturer				PCB soldering terminal			
A		F		APPROVED LILIANJIANG 2018.06.14		≥5 ±0.35											
1		2		3		4		5		6		7		8			



108 100 35 1 D4

Pressing hole specification: M4  
Mold number: C039-H  
Pin height: 3.5mm  
Height above the board: 10.0mm  
Specification size: 10\*8mm

ITEM DESCRIPTION MATERIAL QTY FINISH/COLOR								FIRST VIEW		The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM		TITLE::			
A	Subject	H62(Y2)	1	tin plating						SCALE 1:1 UNIT mm		10*8-H10.0+3.5mm (M4)			
B	Gasket	SPCC	1	tin plating		GENERAL TOLERANCE						DWG NO: 108-P034			
						≥0~2<	±0.15					PART NO: 108-2018101			
					DESIGN	WANGGUIFA	2018.06.12	≥2~5<	±0.25			MODEL NO: 108100351D4			
					CHECKED	ZHENGUILAN	2018.06.12	≥0~2<	±0.15	SAMZO COMPONENTS		NAME:			
F					APPROVED	LILIANJIANG	2018.06.14	≥5	±0.35	Electronic switch and connector manufacturer		PCB soldering terminal			