



SAMZO REAC/ROHS

技术要求:

Technical requirements:



- 打铜底0.5-1UM, 镍底1-3UM, 哑锡3-5UM。
Copper base 0.5 - 1 UM, nickel base 1-3UM, matte tin 3 - 5 UM.
- 不得有脚变形, 毛刺等缺陷。
There shall be no defects such as pin deformation and burrs.
- 插脚尖部符合可焊性要求。
The tip of the insertion pin shall meet the solderability requirements.
- 螺纹需符合通止规要求。
The thread shall meet the requirements of the go and no-go gauge.
- 材质: 黄铜H62。
Material: Brass H62.
- 过载电流: 60A
Overload current: 60A
- 螺孔为 M4
The screw holes M4
- 未标注尺寸公差值按GB/T1184-1996H级
Unmarked dimensional tolerance values are in accordance with Grade H of GB/T1184-1996
- 螺丝扭力: 2.5Nm
Screw torque: 2.5Nm



810 80 30 1 D4

Pressing hole specification: M4
Mold number: C037-H
Pin height: 3.0mm
Height above the board: 8.0mm
Specification size: 8*10mm


REV	ECN NO	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2018.06.12



PCB LAYOUT

ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR					
A	Subject	H62(Y2)	1	tin plating					
B	Gasket	SPCC	1	tin plating					
							GENERAL TOLERANCE		
							$\geq 0 \sim 2 <$	± 0.15	
							$\geq 2 \sim 5 <$	± 0.25	
							$\geq 0 \sim 2 <$	± 0.15	
F					DESIGN	WANGGUIFA	2018.06.12	≥ 5	± 0.35
						CHECKED	ZHENGUILAN	2018.06.12	
						APPROVED	LILIANJIANG	2018.06.14	

FIRST VIEW



The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.KKK-JP.COM

TITLE::

8*10-H8.0+3.0mm (M4)

DWG NO: 810-P031

PART NO: 810-2021101

MODEL NO: 81080301D4

NAME:

PCB soldering terminal

SAMZO COMPONENTS
Electronic switch and connector manufacturer