

Features

- Advance SGT MOS Technology
- 100% EAS Guaranteed
- Fast Switching Speed
- Green Device Available


Product Summary

V_{DS}	100	V
$R_{DS(ON),typ}$	6.6	m Ω
I_D	85	A

Applications

- High Frequency Switching and Synchronous Rectification
- DC/DC Converter

TO-263 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	100	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_C=25^\circ C$	Continuous Drain Current ^{1,6}	85	A
$I_D@T_C=100^\circ C$	Continuous Drain Current ^{1,6}	62	A
I_{DM}	Pulsed Drain Current ²	330	A
EAS	Single Pulse Avalanche Energy ³	41	mJ
I_{AS}	Avalanche Current	28	A
$P_D@T_C=25^\circ C$	Total Power Dissipation ⁴	130	W
T_{STG}	Storage Temperature Range	-55 to 175	$^\circ C$
T_J	Operating Junction Temperature Range	-55 to 175	$^\circ C$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-Ambient ¹	---	50	$^\circ C/W$
$R_{\theta JC}$	Thermal Resistance Junction-Case ¹	---	1.2	$^\circ C/W$



Electrical Characteristics (T_J=25 °C, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250uA	100	---	---	V
R _{DS(ON)}	Static Drain-Source On-Resistance ²	V _{GS} =10V, I _D =13.5A	---	6.6	9	mΩ
V _{GS(th)}	Gate Threshold Voltage	V _{GS} =V _{DS} , I _D =250uA	2.0	2.8	4.0	V
I _{DSS}	Drain-Source Leakage Current	V _{DS} =80V, V _{GS} =0V, T _J =25°C	---	---	1	uA
		V _{DS} =80V, V _{GS} =0V, T _J =55°C	---	---	5	
I _{GSS}	Gate-Source Leakage Current	V _{GS} =±20V, V _{DS} =0V	---	---	±100	nA
g _{fs}	Forward Transconductance	V _{DS} =5V, I _D =20A	---	80	---	S
Q _g	Total Gate Charge (10V)	V _{DS} =50V, V _{GS} =10V, I _D =13.5A	---	45	---	nC
Q _g	Total Gate Charge (4.5V)		---	19.3	---	
Q _{gs}	Gate-Source Charge		---	9.5	---	
Q _{gd}	Gate-Drain Charge		---	4.8	---	
T _{d(on)}	Turn-On Delay Time	V _{DD} =50V, V _{GS} =10V, R _G =3Ω, I _D =13.5A	---	10	---	ns
T _r	Rise Time		---	6.5	---	
T _{d(off)}	Turn-Off Delay Time		---	45	---	
T _f	Fall Time		---	7.5	---	
C _{iss}	Input Capacitance	V _{DS} =50V, V _{GS} =0V, f=1MHz	---	3220	---	pF
C _{oss}	Output Capacitance		---	695	---	
C _{rss}	Reverse Transfer Capacitance		---	26	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I _S	Continuous Source Current ^{1,5,6}	V _G =V _D =0V, Force Current	---	---	80	A
V _{SD}	Diode Forward Voltage ²	V _{GS} =0V, I _S =1A, T _J =25°C	---	---	1.1	V
t _{rr}	Reverse Recovery Time	I _F =13.5A, di/dt=100A/μs,	---	33	---	nS
Q _{rr}	Reverse Recovery Charge	T _J =25°C	---	150	---	nC

Note :

1. The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
2. The data tested by pulsed, pulse width ≤ 300us, duty cycle ≤ 2%
3. The EAS data shows Max. rating. The test condition is V_{DD}=25V, V_{GS}=10V, L=0.1mH, I_{AS}=28A
4. The power dissipation is limited by junction temperature
5. The data is theoretically the same as I_D and I_{DM}, in real applications, should be limited by total power dissipation.
6. The maximum current rating is package limited.



N-Ch 100V Fast Switching MOSFETs

Typical Characteristics




Fig.1 Typical Output Characteristics




Fig.2 On-Resistance vs. G-S Voltage




Fig.3 Source-Drain Forward Characteristics




Fig.4 Gate-Charge Characteristics




Fig.5 Normalized $V_{GS(th)}$ vs. T_J




Fig.6 Normalized $R_{DS(on)}$ vs. T_J



N-Ch 100V Fast Switching MOSFETs




Fig.7 Capacitance




Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform





Fig.11 Unclamped Inductive Switching Waveform

Ordering Information

Part Number	Package code	Packaging
HSH0048A	TO-263	800/Tape&Reel

TO-263 Package Outline



COMMON DIMENSIONS(UNIT OF MEASURE - MM)

SYMBOL	MIN	NOM	MAX
A	4.37	4.57	4.77
A1	0.00	-	0.25
b	0.70	0.83	0.96
b1	1.00	1.24	1.47
C	0.35	0.45	0.55
C1	1.25	1.30	1.35
D	8.50	8.90	9.30
D1	7.50	8.00	8.50
H	14.7	15.20	15.7
E	9.80	10.08	10.4
E1	7.35	7.80	8.25
e1	4.93	5.08	5.23
L	2.00	2.30	2.60
L1	4.50	4.75	5.00
L2	1.30	1.53	1.75
L3	1.10	1.29	1.47
e	2.54 BSC		
θ	13°TYP		



HSH0048A Marking:

