


1		2		3		4		5		6		7		8	
SAMZO		REAC/ROHS								REV	ECN NO	DESCRIPTION	DESIGN	APPROVAL	DATE
										A1	NEW	Replace frame			2013.02.12

技术要求:
 Technical requirements:
 1.打铜底0.5-1UM,镍底1-3UM,亮锡3-5UM。
 Copper Underlayer: 0.5-1 μm, Nickel Underlayer: 1-3 μm, Matte Tin: 3-5 μm
 2.不得有脚变形, 毛刺等缺陷。
 There shall be no defects such as pin deformation and burrs.
 3.插脚尖部符合可焊性要求。
 The tip of the insertion pin shall meet the solderability requirements.
 4.螺纹需符合通止规要求。
 The thread shall meet the requirements of the go and no-go gauge.
 5.材质: 黄铜H62。
 Material: Brass H62.
 6.过载电流: 70A
 Overload current: 70A
 7.牙孔规格 M5
 The specification of the threaded hole M5
 8.未标注尺寸公差值按GB/T1184-1996H级
 Unmarked dimensional tolerance values are in accordance with Grade H of GB/T1184-1996
 9.螺丝扭力: 2.0Nm
 Screw torque: 2.8Nm
 10.盐雾试验: 48小时
 Salt spray test: 48H

10300 31 S 1 L5

Pressing hole specification: M5
 Mold number: S002-H
 Board Mounting Type: SMT
 Height above the board: 3.1mm
 Specification size: 10*30mm



A	ITEM	DESCRIPTION	MATERIAL	QTY	FINISH/COLOR	FIRST VIEW				The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts. WWW.KKK-JP.COM		TITLE: 10*30*3.1mm 4pin SMT H62		
	A	Subject	Brass H62	1	tin plating	GENERAL TOLERANCE				SCALE 1:1 UNIT mm		DWG NO: 10300H-P002		
						DESIGN	WANGGUIFA	2018.06.12	≥0~2<	±0.15	PART NO: 10300-16010		MODEL NO: 1030031S1L5	
						CHECKED	ZHENGUILAN	2018.06.12	≥2~5<	±0.25	NAME: PCB soldering terminal			
						APPROVED	LILIANJIANG	2018.06.14	≥0~2<	±0.15				
	F							≥5	±0.35	SAMZO COMPONENTS				
										Electronic switch and connector manufacturer				