


1. External Dimensions (Unit:mm)



TYPEA	METRIC	A Max	B Max	C Max	D Typ	Q'Ty / Reel
HWC2012	0805	2.4	1.73	1.52	0.44	2000

2. Part Number Code

HWC	2012	K	1R5	D
Series Name	Dimensions	Reference	Inductance	Internal controls

3. Electrical Characteristics

Part Number	Inductance (nH)/MHz	Inductance Tolerance	Q/MHz Min.	SRF(MHz) Min.	RDC(Ω) Max.	I _{rms} (mA) Max.
HWC2012K1R5D	1500/25	$\pm 10\%$	20/25	160	3.3	150

Notes:

- 1) All test data is referenced to 25°C ambient.
- 2) Operating temperature range -40°C to +125°C (Including self - temperature rise).
- 3) L.Q.SRF:agilent/HP E4991A+agilent/HP16197A.
(the electrical specification test by the smallest gap position)or HP16193A
- 4) Rdc: chroma milliohmmeter 16502, or equivalent.
- 5) I_{rms} :DC current(A) that will cause an approximate ΔT of 40°C.