



Part No	Pin	A	B	C	D
BX-GH1.25-2PJK	2	1.25	2.00	3.75	
BX-GH1.25-3PJK	3	2.50	3.20	5.00	
BX-GH1.25-4PJK	4	3.75	4.30	6.25	
BX-GH1.25-5PJK	5	5.00	4.30	7.50	6.25
BX-GH1.25-6PJK	6	6.25	6.25	8.75	8.75
BX-GH1.25-7PJK	7	7.50	6.25	10.00	8.75
BX-GH1.25-8PJK	8	8.75	6.25	11.25	8.75
BX-GH1.25-9PJK	9	10.00	6.25	12.50	8.75
BX-GH1.25-10PJK	10	11.25	8.30	13.75	10.70
BX-GH1.25-11PJK	11	12.50	8.30	15.00	10.70
BX-GH1.25-12PJK	12	13.75	8.30	16.25	10.70
BX-GH1.25-13PJK	13	15.00	8.30	17.50	10.70
BX-GH1.25-14PJK	14	16.25	8.30	18.75	10.70
BX-GH1.25-15PJK	15	17.50	8.30	20.00	10.70
BX-GH1.25-16PJK	16	18.75	8.30	21.25	

技术要求Specification:

1. 材质Material: PA66 UL94V-0;
2. 额定电流 Current rating:1.0A AC,DC
3. 额定电压 Voltage rating: 50V AC,DC
4. 温度范围 Temperature range:-25℃to+85℃
5. 接触电阻 Contact resistance:<30mΩ
6. 绝缘电阻Insulation resistance:>100MΩ
7. 耐压Withstand voltage:500V AC/minute
8. 塑件表面平整光洁, 无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象。

Plastic surface smooth and clean, no obvious burrsbubbles, distortion, gate strain, lack of material and otherundesirable phenomena.

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA	料号 PART NO.	BX-GH1.25-NPJK	版本 REV.	A											
			X.±0.30	X.*±1*							审核 CHECK	EVA	品名 TITLE	GH1.25MM HOUSING	页次 SHEET	1/1					
			.X±0.20														核准 APPROVAL	JADE	客户料号 CUTM.NO.		
			.XX±0.10																		

