



Part No	Pin	A	B	C
BX-PH2.0-2PWT	2	2.00	8.00	6.80
BX-PH2.0-3PWT	3	4.00	10.00	8.80
BX-PH2.0-4PWT	4	6.00	12.00	10.80
BX-PH2.0-5PWT	5	8.00	14.00	12.80
BX-PH2.0-6PWT	6	10.00	16.00	14.80
BX-PH2.0-7PWT	7	12.00	18.00	16.80
BX-PH2.0-8PWT	8	14.00	20.00	18.80
BX-PH2.0-9PWT	9	16.00	22.00	20.80
BX-PH2.0-10PWT	10	18.00	24.00	22.80
BX-PH2.0-11PWT	11	20.00	26.00	24.80
BX-PH2.0-12PWT	12	22.00	28.00	26.80
BX-PH2.0-13PWT	13	24.00	30.00	28.80
BX-PH2.0-14PWT	14	26.00	32.00	30.80
BX-PH2.0-15PWT	15	28.00	34.00	32.80
BX-PH2.0-16PWT	16	30.00	36.00	34.80

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.0
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 2A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING
			X.±0.20	X'.:±5°	
			.X±0.10	X.X':±3°	审核 CHECK
			.XX±0.05	X.XX':±1°	核准 APPROVAL
					单位 UNITS

EMMA	料号 PART NO.	BX-PH2.0-NPWT	版本 REV.	A
EVA	品名 TITLE	WAFER 2.00 贴片	页次 SHEET	1/1
JADE	客户料号 CUTM.NO.			
MM	比例 SCALE	1:1	Bossie (博锡)	