

General Description

The HSL1N25 is the highest performance trench N-ch MOSFETs with extreme high cell density, which provide excellent $R_{DS(on)}$ and gate charge for most of the synchronous buck converter applications.

The HSL1N25 meet the RoHS and Green Product requirement, 100% EAS guaranteed with full function reliability approved.


Product Summary

V_{DS}	250	V
$R_{DS(ON),max}$	1.2	Ω
I_D	1	A

Features

- Super Low Gate Charge
- Green Device Available
- Excellent $C_{dv/dt}$ effect decline
- Advanced high cell density Trench Technology

SOT-223 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	200	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_A=25^\circ\text{C}$	Continuous Drain Current, $V_{GS} @ 10V^1$	1	A
$I_D@T_A=70^\circ\text{C}$	Continuous Drain Current, $V_{GS} @ 10V^1$	0.7	A
I_{DM}	Pulsed Drain Current ²	4	A
$P_D@T_A=25^\circ\text{C}$	Total Power Dissipation ³	2	W
T_{STG}	Storage Temperature Range	-55 to 150	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	-55 to 150	$^\circ\text{C}$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient ¹	---	65	$^\circ\text{C/W}$
$R_{\theta JC}$	Thermal Resistance Junction-Case ¹	---	35	$^\circ\text{C/W}$

N-Ch 250V Fast Switching MOSFETs
Electrical Characteristics ($T_J=25^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	250	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance ²	$V_{GS}=10V$, $I_D=1A$	---	1000	1200	$m\Omega$
$R_{DS(ON)}$	Static Drain-Source On-Resistance ²	$V_{GS}=4.5V$, $I_D=0.5A$	---	1100	1300	$m\Omega$
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	1	1.8	3	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=250V$, $V_{GS}=0V$, $T_J=25^\circ\text{C}$	---	---	1	μA
		$V_{DS}=250V$, $V_{GS}=0V$, $T_J=125^\circ\text{C}$	---	---	100	
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=10V$, $I_D=1A$	---	7.9	---	S
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	1.8	---	Ω
Q_g	Total Gate Charge (10V)	$V_{DS}=100V$, $V_{GS}=10V$, $I_D=1A$	---	12.5	---	nC
Q_{gs}	Gate-Source Charge		---	2	---	
Q_{gd}	Gate-Drain Charge		---	2.5	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=100V$, $V_{GS}=10V$, $R_G=6\Omega$ $I_D=1A$	---	13	---	ns
T_r	Rise Time		---	9	---	
$T_{d(off)}$	Turn-Off Delay Time		---	38	---	
T_f	Fall Time		---	8	---	
C_{iss}	Input Capacitance	$V_{DS}=100V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	670	---	pF
C_{oss}	Output Capacitance		---	14	---	
C_{rss}	Reverse Transfer Capacitance		---	8	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current ^{1,5}	$V_G=V_D=0V$, Force Current	---	---	1	A
I_{SM}	Pulsed Source Current ^{2,5}		---	---	4	A
V_{SD}	Diode Forward Voltage ²	$V_{GS}=0V$, $I_S=1A$, $T_J=25^\circ\text{C}$	---	---	1.2	V
t_{rr}	Reverse Recovery Time	$I_F=1A$, $dI/dt=100A/\mu s$,	---	75	---	nS
Q_{rr}	Reverse Recovery Charge	$T_J=25^\circ\text{C}$	---	270	---	nC

Note :

- 1.The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$
- 3.The power dissipation is limited by 150°C junction temperature
- 4.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.



Typical Characteristics




Fig.1 Typical Output Characteristics




Fig.2 Transfer Characteristics




Fig.3 Power Dissipation




Fig.4 Drain Current




Fig.5 BV_{DS} vs Junction Temperature




Fig.6 $R_{DS(ON)}$ vs Junction Temperature



N-Ch 250V Fast Switching MOSFETs




Fig.7 Gate Charge Waveforms




Fig.8 Capacitance




Fig.9 Body Diode Characteristics





Fig.10 Maximum Safe Operating Area

Ordering Information

Part Number	Package code	Packaging
HSL1N25	SOT-223	3000/Tape&Reel

SOT-223 Package Outline



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	-	1.800	-	0.071
A1	0.020	0.100	0.001	0.004
A2	1.450	1.750	0.057	0.069
b	0.660	0.840	0.026	0.033
b1	2.900	3.100	0.114	0.122
C	0.230	0.350	0.009	0.014
D	6.300	6.700	0.248	0.264
E	6.700	7.300	0.264	0.287
E1	3.300	3.700	0.130	0.146
e	2.300(BSC)		0.091(BSC)	
L	0.750	-	0.030	-
θ	0°	10°	0°	10°

HSL1N25 Marking:

