



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C ~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Housing Nylon66 UL94-V0(2)

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	FG-XH-2Y	2.50	7.30	5.70
3	FG-XH-3Y	5.00	9.80	8.20
4	FG-XH-4Y	7.50	12.30	10.70
5	FG-XH-5Y	10.00	14.80	13.20
6	FG-XH-6Y	12.50	17.30	15.70
7	FG-XH-7Y	15.00	19.80	18.20
8	FG-XH-8Y	17.50	22.30	20.70
9	FG-XH-9Y	20.00	24.80	23.20
10	FG-XH-10Y	22.50	27.30	25.70
11	FG-XH-11Y	25.00	29.80	28.20
12	FG-XH-12Y	27.50	32.30	30.70
13	FG-XH-13Y	30.00	34.80	33.20
14	FG-XH-14Y	32.50	37.30	35.70
15	FG-XH-15Y	35.00	39.80	38.20
16	FG-XH-16Y	37.50	42.30	40.70
17	FG-XH-17Y	40.00	44.80	43.20
18	FG-XH-18Y	42.50	47.30	45.70
19	FG-XH-19Y	45.00	49.80	48.20
20	FG-XH-20Y	47.50	52.30	50.60

			GENERAL TOLERANCE		制 图 DRAWING		深圳市富港科技有限公司			
			DIM	TOL	审 核 CHECK					
			X.X	±0.30	批 准 APPROVAL		产品名称 TITLE	XH (2.5)单排 孔座	版本 REV.	A
1			初版发行		比 例 SCALE		产品料号 PART NO.	FG-XH-NY	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1