


Features

- General rectification
- Low V_F ; Low I_R
- High reliability



SOD123

PIN	DESCRIPTION
1	Cathode
2	Anode



Applications

- surface mount schottky barrier rectifier

Ordering Information

- Shipping Qty:3000/7inch Tape& Reel

Absolute Maximum Ratings ($T_A=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Peak Repetitive Reverse Voltage	V_{RRM}	20	V
RMS Reverse Voltage	V_{RMS}	14	V
Maximum Average Forward Output Current	$I_{F(AV)}$	0.5	A
Peak Forward Surge Current (8.3ms single half sine-wave)	I_{FSM}	5.5	A

Thermal Characteristics

Parameter	Symbol	Value	Unit
Power Dissipation	P_D	500	mW
Operating junction Temperature	T_J	150	$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-55 ~ +150	$^\circ\text{C}$

Electrical Characteristics ($T_A=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Forward Voltage	V_F	$I_F = 0.1\text{A}$	-	-	0.375	V
		$I_F = 0.5\text{A}$	-	-	0.44	
Maximum Peak Reverse Current	I_R	$V_R = 20\text{V}$	-	-	20	μA

Ratings and Characteristic Curves (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)




Fig. 1 Forward Characteristics





Fig. 2 Typical Reverse Characteristic

Outline Drawing - SOD123 (unit: mm)



SOD-123		
Dim	Min	Max
A	1.45	1.75
B	2.55	2.85
C	1.00	1.30
D	0.50	0.60
E	0.25	0.45
H	0.02	0.10
J	0.05	0.15
K	3.55	3.85

Mounting Pad Layout-SOD123 (unit: mm)

