

MF72 SERIES NTC Thermistor Datasheet

Features


- MF72 Series NTC thermistors for inrush current limiting
- Resistance tolerance <20%
- Big material constant(B value),small residual resistance
- Fast response,Long life and high reliability
- Excellent solder ability,Highly stable electrical characteristics

Applications


- Inrush current limiting, e.g. in switch-mode power supplies, soft-start motors
- Switching power-supply, switch power ,ups power
- Electronic energy saving lamps electronic ballast and all kinds of electric heater
- Household electrical appliances, AUDIO-visual equipment
- Communications, electronic motors, lighting

Part Number Code

MF72 XX D-X



Recommended Soldering Conditions



| Item             | Conditions   |
|------------------|--------------|
| Peak Temperature | 265°C        |
| Dipping Time     | 10 secs. Max |
| Soldering        | 1 time       |

Recommendation Reworking Conditions with Soldering Iron

| Item                              | Conditions  |
|-----------------------------------|-------------|
| Temperature of Soldering Iron-tip | 360°C Max   |
| Soldering Time                    | 3 secs. Max |
| Distance from Thermistor          | 2 mm Min    |

# MF72 10D-15

NTC thermistors for inrush current limiting




## Electrical Characteristics (Ta=25°C Unless otherwise specified)

| PARAMETER                      | Symbol             | CONDITION                   | VALUE        | UNIT  |
|--------------------------------|--------------------|-----------------------------|--------------|-------|
| Rated Zero-Power Resistance    | R <sub>25</sub>    | T <sub>a</sub> =25°C ±0.2°C | 10±20%       | Ω     |
| B Constant (Material Constant) | B <sub>25/85</sub> | 25°C /85°C                  | 2800±10%     | K     |
| Max. steady State current      | I <sub>max</sub>   | /                           | 5            | A     |
| Max Shock Capacity             | C <sub>T</sub>     | 240V ac                     | 470          | μF    |
| Thermal Dissipation Constant   | δ                  | stationary in the air       | 21 typ       | mW/°C |
| Thermal Time Constant          | τ                  | stationary in the air       | 85 typ       | sec   |
| Residual Resistance            | /                  | Max.steady State current    | 0.178        | Ω     |
| Operating Temperature Range    | /                  | /                           | -40 to + 150 | °C    |

## Component Materials

| Wrapper                 | Down-lead | Coating color |
|-------------------------|-----------|---------------|
| Modified phenolic resin | Cu Wire   | Black         |

## Physical Dimensions (mm)

|  |  |  |             |         |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------|---------|
| Inside Type                                                                         | Outside Type                                                                        | Straight Type                                                                         |             |         |
| Note: Default inside type for long lead.                                            |                                                                                     |                                                                                       |             |         |
| D (Max mm)                                                                          | L (Min. mm)                                                                         | d (mm)                                                                                | T (Max. mm) | P (mm)  |
| 17.5                                                                                | 15.0                                                                                | 0.8±0.1                                                                               | 6.0         | 7.5±1.0 |

## Ordering Information

| Part Number | DELIVERY MODE | MPQ(PCS) |
|-------------|---------------|----------|
| MF72 10D-15 | Bulk          | 500      |

## ● Electrical Test

| Items                                 | Test Methods and Remarks                                                                                                                                                                                                                                                                                             |
|---------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Nominal Zero-Power Resistance at 25°C | Ambient temperature: $25 \pm 0.2^\circ\text{C}$ ;                                                                                                                                                                                                                                                                    |
| Nominal B Constant                    | Measure the resistance at the ambient temperature of $25 \pm 0.05^\circ\text{C}$ , $50 \pm 0.05^\circ\text{C}$ or $85 \pm 0.05^\circ\text{C}$ .<br>$B(25/50^\circ\text{C}) = \frac{\ln R_{25} - \ln R_{50}}{1/T_{25} - 1/T_{50}} \quad B(25/85^\circ\text{C}) = \frac{\ln R_{25} - \ln R_{85}}{1/T_{25} - 1/T_{85}}$ |
| Thermal Time Constant                 | The total time for the temperature of the thermistor to change by 63.2% of the difference from ambient temperature $T_0$ ( $^\circ\text{C}$ ) to $T_1$ ( $^\circ\text{C}$ ) by the drastic change of the power applied to thermistor from Non-zero Power to Zero-Power state, normally expressed in second(S)        |
| Dissipation Factor                    | The required power which makes the NTC thermistor body temperature raise $1^\circ\text{C}$ through self-heated, normally expressed in milliwatts per degree Celsius (mW/ $^\circ\text{C}$ ) . It can be calculated by the following formula:<br>$\delta = \frac{W}{T - T_0}$                                         |

## ● Reliability Test

| Items                                  | Test Conditions & Methods                                                                                                                                                                   | Requirements                                                                                        |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------|
| Tensile strength of terminals          | Gradually applying the force specified and duration $10 \pm 1\text{s}$<br>Leads Diameter : $0.5 < d \leq 0.8$ , Pull: 10N<br>Leads Diameter : $0.8 < d \leq 1.25$ , Pull: 20N               | No visible damage,<br>$R_{25} \Delta R/R \leq \pm 25\%$                                             |
| Solderability                          | The leads are immersed in a tin fluid 6mm from the thermistor. The tin fluid temperature is $245 \pm 5^\circ\text{C}$ , and the dip soldering time is 2s to 3s.                             | The solder is evenly coated on the surface of the lead immersed part, and the tin area is over 95%. |
| Solder resistance                      | Leads are immersed in a tin fluid at a distance of 6mm from the thermistor. The tin fluid temperature is $260 \pm 5^\circ\text{C}$ , the dip soldering time is $10\text{s} \pm 1\text{s}$ . | No visible damage,<br>$R_{25} \Delta R/R \leq \pm 25\%$                                             |
| Thermal shock                          | Temperature: $-40 \pm 5^\circ\text{C}$ , 30min / cycle, interval time 5min;<br>temperature: $+150 \pm 5^\circ\text{C}$ , 30min / cycle, interval time 5min;<br>5 cycles                     | No visible damage,<br>$R_{25} \Delta R/R \leq \pm 25\%$                                             |
| High temperature storage               | Temperature: $150 \pm 5^\circ\text{C}$ , time: $1000 \pm 24\text{h}$                                                                                                                        | No visible damage,<br>$R_{25} \Delta R/R \leq \pm 25\%$                                             |
| Steady state damp heat                 | Temperature: $-40 \pm 2^\circ\text{C}$ , 90 ~ 95% RH, time: $1000 \pm 24\text{h}$                                                                                                           | No visible damage,<br>$R_{25} \Delta R/R \leq \pm 25\%$                                             |
| Maximum steady state current Life test | $25 \pm 5^\circ\text{C}$ , Maximum steady state current, $1000 \pm 24\text{hrs}$                                                                                                            | No visible damage,<br>$R_{25} \Delta R/R \leq \pm 25\%$                                             |
| Endurance                              | $25 \pm 5^\circ\text{C}$ , Maximum steady state current , Capacitance at 240Vac , 1min on / 5 min off , 1000 cycles                                                                         | No visible damage,<br>$R_{25} \Delta R/R \leq \pm 25\%$                                             |
| Insulation resistance                  | Test voltage 500VDC, duration 1min                                                                                                                                                          | No visible damage,<br>$R_{25} \Delta R/R \leq \pm 25\%$                                             |

## ● Environmental Specification

|                      |                                                                                                                                                                    |
|----------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Storage temperature: | $-10^\circ\text{C}$ to $+40^\circ\text{C}$                                                                                                                         |
| Storage Conditions:  | Light-proof, Hermetically Sealed, Moisture-proof;<br>The components should be left in their original packing to avoid soldering problems due to oxidized contacts. |
| Relative humidity:   | $< 75\% \text{ RH}$                                                                                                                                                |
| Storage period       | The components should be employed within 12 months after delivery, the components should be resealed after opening the packing.                                    |

● Electrical Characteristics (Ta=25°C Unless otherwise specified)

| Items                              | Characteristic Description                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | Characteristic curve                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
|------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Derating Curve of I <sub>max</sub> | When the applied ambient temperature of the product is lower than 0 °C or higher than 25 °C , the maximum allowable working current I <sub>max</sub> should be reduced, and the amount of reduction is shown in the curve below.                                                                                                                                                                                                                                                                                                      | <p>The graph shows the Maximum rated current (%) on the y-axis (0 to 100) versus Ambient temperature (°C) on the x-axis. The curve starts at 0% at T<sub>L</sub>, rises linearly to 100% at 0°C, remains constant at 100% until 25°C, and then decreases linearly to 0% at T<sub>U</sub>. Dashed vertical lines mark 0 and 25 on the x-axis. A dashed horizontal line marks 100 on the y-axis.</p> <p>Remarks:<br/>T<sub>L</sub>=Minimum temperature(°C)<br/>T<sub>U</sub>=Maximum temperature(°C)</p> |
| R-T Characteristic Curve           | R-T characteristic is the relationship between zero-power resistance and bodu temperature of the thermistor .<br>The resistance value of the NTC thermistor is measured under a current with a sufficiently low spontaneous heat.                                                                                                                                                                                                                                                                                                     | <p>The graph shows Resistance on the y-axis (0Ω to 25°C) versus Temperature on the x-axis (-50°C to 200°C). The curve is a smooth, downward-sloping line. A red horizontal line is drawn at the 25°C mark on the y-axis, and a red vertical line is drawn at the 25°C mark on the x-axis, intersecting the curve.</p>                                                                                                                                                                                  |
| V-I Static Characteristic curve    | In regions with low current, as the current gradually increases, the voltage of the ohmic contact also gradually rises. By dissipating heat from the surface of the thermistor and other parts, the self-heating caused by the current flow does not lead to an increase in the resistance temperature.<br>However, when the heat generation is large, the temperature of the thermistor itself rises and the resistance value decreases. In such regions, the proportional relationship between current and voltage no longer holds. | <p>The graph shows Voltage (v) on the y-axis versus Current (mA) on the x-axis. The curve is a smooth, downward-sloping line. The title "(25°C in Air)" is located at the top right of the graph area.</p>                                                                                                                                                                                                                                                                                             |