


PRODUCT CHARACTERISTICS

V_{DSS}	800V
$R_{DS(ON)}$ Typ(@ $V_{GS}=15V$)	380m Ω
Qg@typ	21.3nC
I_D	11A




APPLICATIONS

- *Switch Mode Power Supplies
- *High Voltage DC/DC Converters
- *Battery Chargers
- *Motor Drivers

FEATURE

- *Low On-Resistance With High Blocking Voltage
- *Low Capacitances With High -Speed Switching
- *Low Reverse Recovery(Qrr)
- *Easy to Parallel and Simple to Drive



TO-252

ORDER INFORMATION

Order Codes		Package	Packing
Halogen-Free	Halogen		
N/A	MOT80CH380D	TO-252	2500 pieces/Reel

ABSOLUTE MAXIMUM RATINGS($T_A=25^{\circ}C$, unless otherwise specified)

Parameter	Symbol	Ratings	Unit
Drain-Source Voltage	V_{DSS}	800	V
Gate-Source Voltage	V_{GSS}	-10/+20	V
Recommended Operation Voltage Of Gate to Source	V_{GSOP}	0/+18	V
Drain Current Continuous(@ $V_{GS}=15V$, $T_c=25^{\circ}C$)	I_D	11	A
Drain Current Continuous(@ $V_{GS}=15V$, $T_c=175^{\circ}C$)	I_D	9	A
Drain Current Pulsed(@ $V_{GS}=15V$, $T_c=25^{\circ}C$)	I_{DM}	22	A
Power Dissipation	P_D	52	W
Junction Temperature	T_J	+175	$^{\circ}C$
Storage Temperature	T_{STG}	-55~ +175	$^{\circ}C$

THERMAL CHARACTERISTICS

Parameter	Symbol	Typ	Unit
Junction to Case	R_{thJC}	2.9	$^{\circ}C/W$

■ ELECTRICAL CHARACTERISTICS ($T_C=25^{\circ}\text{C}$, unless otherwise noted)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Off characteristics						
Drain to Source Breakdown Voltage	V _{DSS}	V _{GS} =0V, I _D =500μA	800	-	-	V
Drain to Source Leakage Current	I _{DSS}	V _{DS} =800V, V _{GS} =0V	-	-	10	μA
Gate to Source Forward Leakage	I _{GSS}	V _{DS} =0V, V _{GS} =18V	-	-	250	nA
On characteristics						
Drain to Source On-Resistance	R _{DS(ON)}	V _{GS} =15V, I _D =5A	-	380	500	mΩ
		V _{GS} =15V, I _D =5A, T _J =175°C	-	325	-	mΩ
		V _{GS} =18V, I _D =5A	-	260	-	mΩ
		V _{GS} =18V, I _D =5A, T _J =175°C	-	270	-	mΩ
Gate Threshold Voltage	V _{GS(TH)}	V _{DS} =V _{GS} , I _D =1.8mA	2.7	-	4.5	V
Dynamic characteristics						
Gate capacitance	R _g	V _{AC} =25mV ,f=1.0MHz	-	5	-	Ω
Input Capacitance	C _{iss}	V _{DS} =30V, V _{GS} =0V f=1.0MHz	-	267	-	pF
Output Capacitance	C _{oss}		-	61	-	pF
Reverse Transfer Capacitance	C _{rss}		-	5	-	pF
Resistive Switching Characteristics						
Turn-on Delay Time	t _{d(ON)}	I _D =5A, V _{DS} =500V R _G =10 Ω ,V _{GS} =0/15V	-	24	-	ns
Rise Time	t _r		-	42	-	ns
Turn-off Delay Time	t _{d(OFF)}		-	26.8	-	ns
Fall Time	t _f		-	76	-	ns
Total Gate Charge	Q _g	I _D =5A, V _{DS} =500V V _{GS} =0/15V	-	21.3	-	nC
Gate to Source Charge	Q _{gs}		-	6.7	-	nC
Gate to Drain("Miller") Charge	Q _{gd}		-	11.5	-	nC
Source-Drain Diode Characteristics						
Continuous Source Current(Body Diode)	I _s		-	-	11	A
Diode Forward Voltage	V _{SD}	I _{SD} =3A, V _{GS} =0V	-	3.5	-	V
Reverse Recovery Time	t _{rr}	I _{SD} =5A, T _J =25 °C dI/dt=530A/μs	-	17.8	-	ns
Reverse Recovery Charge	Q _{rr}		-	33.7	-	nC

■ TYPICAL CHARACTERISTICS




Figure 1: Output Characteristics($T_J=25^\circ\text{C}$)




Figure 2: Output Characteristics($T_J=175^\circ\text{C}$)




Figure 3: Typical Transfer Characteristics




Figure 4: Normalized On-Resistance vs Temperature




Figure 5: Normalized On-Resistance vs. Drain Current For Various Temperature




Figure 6: Normalized Threshold Voltage vs. Temperature

■ TYPICAL CHARACTERISTICS(Cont.)




Figure 7: Capacitance vs. Drain-Source Voltage




Figure 8: Body Diode Characteristics

Technical drawing of a mechanical part, showing front and side views with dimensions.

Front View Dimensions:

- Top left corner: 1.0 ± 0.15 (width), $0.05^{+0.15}_{-0.03}$ (height)
- Top center: 5.33 ± 0.20 (width)
- Top right corner: 1.78 ± 0.2 (height)
- Bottom left corner: 6.6 (width), 0.8 ± 0.2 (height)
- Bottom center: 2.286 (width)
- Bottom right corner: 0.840 ± 0.1 (height)
- Overall width: 6.1 ± 0.1
- Overall height: 10.2 ± 0.3
- Left side: 1.2 ± 0.1 (width), $0.76^{+0.10}_{-0.02}$ (height)
- Top left corner radius: $R1.438$

Side View Dimensions:

- Top left corner: $1.062^{+0.35}_{-0.1}$ (width), 0.5 (height)
- Top center: 2.3 ± 0.15 (width)
- Top right corner: 0.5 (height)
- Bottom left corner: 3.1 ± 0.3 (width)
- Bottom center: $0.5^{+0.1}_{-0}$ (width)
- Bottom right corner: 1.65 (height)
- Overall width: 10.2 ± 0.3
- Overall height: 10.2 ± 0.3
- Left side: 0.76 (width)
- Top left corner radius: $R1.438$