

## Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	$I_D$
100V	5.9mΩ@10V	92A
	7.6mΩ@4.5V	



合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务

www.siliup.com


## Feature

- Fast Switching
- Low Gate Charge and R<sub>ds(on)</sub>
- Advanced Split Gate Trench Technology
- 100% Single Pulse avalanche energy Test

## Applications


- Power switching application
- Battery management
- Uninterruptible power supply

## Package



PDFN5X6-8L

## Circuit diagram



## Marking



SP010N06GNK : Product code  
 \*\* : Week code

## Order Information

Device	Package	Unit/Tape
SP010N06GNK	PDFN5X6-8L	5000

**Absolute maximum ratings (Ta=25°C, unless otherwise noted)**

Parameter	Symbol	Rating	Unit
Drain-Source Voltage	V <sub>DS</sub>	100	V
Gate-Source Voltage	V <sub>GS</sub>	±20	V
Continuous Drain Current (Tc=25°C)	I <sub>D</sub>	92	A
Continuous Drain Current (Tc=100°C)	I <sub>D</sub>	58.2	A
Pulsed Drain Current	I <sub>DM</sub>	368	A
Single Pulse Avalanche Energy <sup>1</sup>	E <sub>AS</sub>	212	mJ
Power Dissipation (Tc=25°C)	P <sub>D</sub>	102	W
Power Dissipation (Tc=100°C)	P <sub>D</sub>	40	W
Thermal Resistance Junction-to-Case	R <sub>θJC</sub>	1.18	°C/W
Storage Temperature Range	T <sub>STG</sub>	55 to 150	°C
Operating Junction Temperature Range	T <sub>J</sub>	55 to 150	°C


**Electrical characteristics (Ta=25°C, unless otherwise noted)**

Characteristics	Symbol	Test Condition	Min	Typ	Max	Unit
<b>Static Characteristics</b>						
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	I <sub>D</sub> = 250μA, V <sub>GS</sub> = 0V	100	-	-	V
Drain Cut-Off Current	I <sub>DSS</sub>	V <sub>DS</sub> = 80V, V <sub>GS</sub> = 0V	-	-	1	uA
Gate Leakage Current	I <sub>GSS</sub>	V <sub>GS</sub> = ±20V, V <sub>DS</sub> = 0V	-	-	±0.1	nA
Gate Threshold Voltage	V <sub>GS(th)</sub>	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250μA	1.3	1.7	2.3	V
Drain-Source ON Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> = 10V, I <sub>D</sub> = 30A	-	5.9	7.5	mΩ
		V <sub>GS</sub> = 4.5V, I <sub>D</sub> = 25A	-	7.6	10.0	
Gate Resistance	R <sub>G</sub>	V <sub>DS</sub> =50V, V <sub>GS</sub> =0V, f=1MHz	-	1.92	-	Ω
<b>Dynamic Characteristics</b>						
Input Capacitance	C <sub>iss</sub>	V <sub>DS</sub> = 50V, V <sub>GS</sub> = 0V, f = 1.0MHz	-	2252	-	pF
Output Capacitance	C <sub>oss</sub>		-	453	-	
Reverse Transfer Capacitance	C <sub>riss</sub>		-	15	-	
Total Gate Charge	Q <sub>g</sub>	V <sub>DS</sub> =50V, V <sub>GS</sub> =10V, I <sub>D</sub> =50A	-	38	-	nC
Gate-Source Charge	Q <sub>gs</sub>		-	9	-	
Gate-Drain Charge	Q <sub>gd</sub>		-	8	-	
Gate Plateau Voltage	V <sub>plateau</sub>		-	3.78	-	
<b>Switching Characteristics</b>						
Turn-On Delay Time	t <sub>d(on)</sub>	V <sub>GS</sub> = 50V, V <sub>DS</sub> = 50V, I <sub>D</sub> =50A R <sub>G</sub> = 4.7Ω	-	12	-	nS
Rise Time	t <sub>r</sub>		-	23	-	
Turn-Off Delay Time	t <sub>d(off)</sub>		-	36	-	
Fall Time	t <sub>f</sub>		-	10	-	
<b>Drain-Source Body Diode Characteristics</b>						
Source-Drain Diode Forward Voltage	V <sub>SD</sub>	V <sub>GS</sub> =0V, I <sub>S</sub> =1A, T <sub>J</sub> =25°C	-	-	1.2	V
Maximum Body-Diode Continuous Current	I <sub>S</sub>		-	-	92	A
Reverse Recovery Time	T <sub>rr</sub>	I <sub>S</sub> =20A, di/dt=100A/us, T <sub>J</sub> =25°C	-	49	-	nS
Reverse Recovery Charge	Q <sub>rr</sub>		-	68	-	nC


**Note:**

- The EAS test condition is VDD=50V, VGS=10V, L=0.5mH, RG=25Ω


### Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




On-Resistance vs Gate to Source Voltage




Normalized On-Resistance




RDS(on) VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage




Normalized Threshold voltage




Current dissipation



Power dissipation







Maximum Transient Thermal Impedance




Safe Operation Area

**Test Circuit**



**Temperature Profile for IR Reflow Soldering(Pb-Free)**



Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
<b>Preheat &amp; Soak</b>		
Temperature min (T <sub>smin</sub> )	100°C	150°C
Temperature max (T <sub>smax</sub> )	150°C	200°C
Time (T <sub>smin</sub> to T <sub>smax</sub> ) (t <sub>s</sub> )	60-120 seconds	60-120 seconds
Average ramp-up rate (T <sub>smax</sub> to T <sub>p</sub> )	3 °C/second max.	3°C/second max.
Liquidous temperature (T <sub>L</sub> )	183 °C	217°C
Time at liquidous (t <sub>L</sub> )	60-150 seconds	60-150 seconds
Peak package body Temperature e (T <sub>p</sub> )*	See Classification Temp in table 1	See Classification Temp in table 2
Time (t <sub>p</sub> )** within 5°C of the specified classification temperature (T <sub>c</sub> )	20** seconds	30** seconds
Average ramp-down rate (T <sub>p</sub> to T <sub>smax</sub> )	6 °C/second max.	6 °C/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.
* Tolerance for peak profile Temperature (T <sub>p</sub> ) is defined as a supplier minimum and a user maximum. ** Tolerance for time at peak profile temperature (t <sub>p</sub> ) is defined as a supplier minimum and a user maximum		


Table 1. SnPb Eutectic Process – Classification Temperatures (T<sub>c</sub>)

Package Thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2. Pb-free Process – Classification Temperatures (T<sub>c</sub>)


Package Thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> 350-2000	Volume mm <sup>3</sup> >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm – 2.5 mm	260 °C	250 °C	245 °C
≥2.5 mm	250 °C	245 °C	245 °C

**PDFN5X6-8L Embossed Carrier Tape**




Dimensions are in millimeter										
Pkg type	A	B	C	d	E	F	P0	P	P1	W
PDFN5X6-8L	6.30	5.30	1.10	Φ1.50	1.75	5.50	4.00	8.00	2.00	12.00

**PDFN5X6-8L Tape Leader and Trailer**





**PDFN5X6-8L Reel**



Dimensions are in millimeter						
Reel Option	D	D1	D2	G	W1	W2
13" Dia	Ø330.00	100.00	13.00	1.90	17.60	12.40

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)
5,000 pcs	13 inch	5,000 pcs	340×336×29	50,000 pcs	353×346×365

**PDFN5X6-8L Package Information**



Side View [侧视图]

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.120	0.035	0.044
b	0.330	0.510	0.013	0.020
C	0.110	0.340	0.004	0.013
D	4.700	5.260	0.185	0.207
D1	4.700	5.100	0.185	0.201
D2	3.560	4.500	0.140	0.177
E	5.750	6.250	0.226	0.246
E1	5.600	6.000	0.220	0.236
E2	3.180	3.660	0.125	0.144
e	1.170	1.370	0.046	0.054
L	0.350	0.710	0.014	0.028
L1	0.060	0.200	0.002	0.008
H	0.350	0.710	0.014	0.028